

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.03	40.1	40.0
200.0	0.04	37.6	37.7
300.0	0.05	36.3	36.6
400.0	0.06	37.0	37.3
500.0	0.07	39.3	40.1
600.0	0.08	43.7	46.5
700.0	0.09	44.9	46.9
800.0	0.09	40.7	40.5
900.0	0.10	36.5	36.2
1000.0	0.11	34.5	34.2
1100.0	0.11	33.7	33.6
1250.0	0.12	35.0	35.0
1500.0	0.13	47.6	44.8
1750.0	0.15	34.3	33.7
2000.0	0.16	31.0	30.6
2001.0	0.16	31.5	31.1
2250.0	0.17	38.6	36.6
2500.0	0.17	39.9	37.3
2750.0	0.19	30.4	29.8
3000.0	0.19	29.4	29.1
3250.0	0.20	38.0	34.6
3500.0	0.21	37.4	33.3
3750.0	0.22	29.0	28.0
4000.0	0.23	29.7	29.2
4250.0	0.23	36.8	36.9
4500.0	0.24	35.1	34.2
5000.0	0.25	32.7	33.0
5500.0	0.26	32.9	33.3
6000.0	0.26	34.3	33.8
6500.0	0.28	40.8	34.6
7000.0	0.28	33.3	37.5
7500.0	0.30	37.8	40.1
8000.0	0.31	32.7	40.9
8500.0	0.31	34.1	43.3
9000.0	0.32	39.5	43.3
9500.0	0.33	36.4	34.4
10000.0	0.34	26.8	28.7
10500.0	0.35	28.4	29.5
11000.0	0.36	28.0	28.4
11500.0	0.37	27.2	27.4
12000.0	0.39	26.1	25.6
12500.0	0.40	24.8	24.1
13000.0	0.43	23.2	22.2
13500.0	0.43	24.1	22.9
14000.0	0.45	23.3	21.5
14500.0	0.47	22.9	21.0
15000.0	0.49	21.3	22.3
15500.0	0.52	20.8	21.6
16000.0	0.51	21.3	21.4
16500.0	0.55	20.5	20.6
17000.0	0.51	22.9	21.4
17500.0	0.50	25.5	24.1
18000.0	0.48	28.9	29.4