

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.04	48.2	47.0
200.0	0.06	46.1	44.2
300.0	0.07	44.4	43.2
400.0	0.08	44.6	42.7
500.0	0.09	43.6	43.0
600.0	0.10	46.6	45.7
700.0	0.12	48.2	51.7
800.0	0.13	47.0	51.9
900.0	0.14	41.7	42.8
1000.0	0.14	39.1	39.3
1100.0	0.15	38.1	38.4
1250.0	0.16	39.1	40.3
1500.0	0.18	46.3	44.4
1750.0	0.19	35.9	35.0
2000.0	0.20	39.9	41.0
2001.0	0.20	40.0	41.1
2250.0	0.22	39.9	37.5
2500.0	0.23	35.4	33.9
2750.0	0.24	52.2	40.2
3000.0	0.26	33.8	34.2
3250.0	0.26	32.1	32.7
3500.0	0.27	40.8	36.6
3750.0	0.28	28.1	28.6
4000.0	0.28	29.0	29.8
4250.0	0.30	48.7	37.0
4500.0	0.31	32.2	30.8
5000.0	0.32	42.7	47.4
5500.0	0.33	36.4	39.6
6000.0	0.33	40.1	39.3
6500.0	0.34	36.4	40.6
7000.0	0.36	37.9	40.4
7500.0	0.38	38.6	43.6
8000.0	0.40	66.1	45.3
8500.0	0.41	38.7	56.9
9000.0	0.41	33.7	29.7
9500.0	0.44	28.6	28.7
10000.0	0.44	42.2	33.9
10500.0	0.44	30.0	38.1
11000.0	0.46	30.0	28.2
11500.0	0.47	26.1	26.2
12000.0	0.47	37.1	28.8
12500.0	0.49	32.9	29.7
13000.0	0.45	26.0	27.0
13500.0	0.50	25.3	24.1
14000.0	0.57	37.2	27.9
14500.0	0.59	31.9	29.5
15000.0	0.56	28.4	27.4
15500.0	0.58	24.6	26.4
16000.0	0.61	36.4	31.9
16500.0	0.55	37.7	37.5
17000.0	0.63	29.5	38.4
17500.0	0.63	31.0	29.8
18000.0	0.73	19.8	20.4