

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMP-FEMALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMP-FEMALE 2 RETURN LOSS (dB)
10	0.02	47.8	47.8
50	0.04	45.3	45.3
100	0.05	42.0	42.1
200	0.08	37.3	37.3
300	0.10	36.1	36.1
400	0.12	36.4	36.4
500	0.13	38.8	38.8
600	0.14	45.7	43.9
700	0.15	45.8	44.1
800	0.16	39.0	38.8
900	0.17	33.3	33.6
1000	0.18	32.2	32.2
1100	0.19	34.5	34.4
1250	0.21	38.3	41.3
1500	0.23	29.8	30.2
1750	0.23	35.1	37.9
2000	0.26	28.1	28.6
2001	0.26	28.1	28.6
2250	0.27	32.1	35.9
2500	0.29	27.2	28.9
2750	0.29	30.5	33.1
3000	0.31	26.6	29.1
3250	0.33	29.8	30.8
3500	0.35	27.0	30.9
3750	0.35	27.7	27.5
4000	0.36	27.3	30.8
4250	0.37	27.9	27.7
4500	0.38	27.9	31.3
5000	0.40	28.0	29.8
5500	0.42	29.3	30.2
6000	0.43	27.2	27.5
6500	0.45	27.4	27.0
7000	0.47	28.4	29.1
7500	0.48	25.8	27.2
8000	0.50	25.6	28.4
8500	0.50	24.5	27.0
9000	0.47	24.9	26.9
9500	0.53	26.1	26.2
10000	0.49	27.2	25.7
10500	0.54	26.7	26.6
11000	0.56	27.7	26.7
11500	0.60	29.5	26.1
12000	0.60	28.3	26.4
12500	0.62	27.8	27.7
13000	0.61	26.0	27.5
13500	0.63	27.5	30.7
14000	0.64	26.4	31.0
14500	0.64	26.4	32.2
15000	0.66	27.6	31.3
15500	0.66	28.1	32.5
16000	0.66	28.8	32.4
16500	0.63	26.8	27.6
17000	0.71	26.2	27.2
17500	0.71	26.9	28.0
18000	0.59	25.4	28.2