

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-FEMALE BULKHEAD RETURN LOSS (dB)
100.0	0.03	46.0	45.8
200.0	0.04	42.3	38.3
400.0	0.06	44.0	38.7
500.0	0.07	57.7	40.6
600.0	0.08	45.6	36.2
800.0	0.09	40.2	33.9
900.0	0.10	45.0	39.0
1000.0	0.10	50.6	35.0
1200.0	0.11	38.3	34.1
1400.0	0.12	51.1	37.7
1600.0	0.13	37.4	35.9
1800.0	0.14	48.0	37.6
2000.0	0.15	37.1	34.9
2200.0	0.15	41.9	35.1
2400.0	0.16	38.5	35.0
2600.0	0.15	38.3	31.4
2800.0	0.18	48.6	31.2
3000.0	0.17	44.0	30.8
3200.0	0.20	45.2	30.0
3400.0	0.20	40.9	32.1
3600.0	0.23	40.0	29.8
3800.0	0.22	35.1	30.6
4000.0	0.21	35.2	27.5
4200.0	0.22	31.8	25.8
4400.0	0.22	32.2	23.3
4600.0	0.22	31.5	23.1
4800.0	0.25	29.2	21.5
5000.0	0.18	29.9	21.6
5200.0	0.27	27.0	20.6
5400.0	0.29	28.6	21.0
5600.0	0.30	27.2	20.6
5800.0	0.33	27.0	21.7
6000.0	0.32	27.0	21.1
6200.0	0.30	25.7	23.9
6400.0	0.30	27.3	24.0
6600.0	0.23	24.7	28.4
6800.0	0.30	26.9	28.1
7200.0	0.35	26.8	31.1
7400.0	0.36	25.5	30.4
7600.0	0.39	26.1	28.5
7800.0	0.35	25.7	24.7
8000.0	0.37	26.0	22.8
8200.0	0.33	25.6	21.4
8400.0	0.34	25.9	19.8
8600.0	0.36	26.8	19.3
8800.0	0.42	24.8	18.7
9000.0	0.39	26.3	18.8
9200.0	0.40	29.7	18.8
9400.0	0.33	26.0	18.5
9600.0	0.38	30.3	21.2
9800.0	0.41	30.2	21.5
10000.0	0.48	33.6	21.6
10200.0	0.48	33.6	21.6
10400.0	0.41	32.9	21.9
10600.0	0.40	27.7	19.8
10800.0	0.40	28.4	26.2
11000.0	0.46	32.9	21.5
11200.0	0.41	27.5	26.8
11400.0	0.44	30.7	24.5
12500.0	0.40	20.9	19.9