

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.05	41.0	42.5
200.0	0.08	41.6	45.0
300.0	0.10	47.1	62.2
400.0	0.11	51.3	48.3
500.0	0.13	46.7	44.6
600.0	0.15	46.2	47.3
700.0	0.16	52.0	58.8
800.0	0.17	53.5	51.7
900.0	0.18	46.8	48.6
1000.0	0.19	43.9	67.5
1100.0	0.20	44.7	48.1
1250.0	0.22	49.8	40.6
1500.0	0.24	45.3	46.9
1750.0	0.26	42.7	41.5
2000.0	0.28	42.8	39.4
2001.0	0.28	42.7	39.4
2250.0	0.30	54.8	45.6
2500.0	0.32	35.9	34.7
2750.0	0.33	40.6	41.0
3000.0	0.35	40.7	35.5
3250.0	0.36	46.6	43.1
3500.0	0.38	34.8	33.4
3750.0	0.40	46.2	42.3
4000.0	0.41	35.4	35.5
4250.0	0.42	39.2	35.0
4500.0	0.43	38.1	39.3
5000.0	0.46	41.6	41.6
5500.0	0.48	34.6	33.9
6000.0	0.52	29.1	29.6
6500.0	0.55	22.9	23.1
7000.0	0.55	28.5	28.4
7500.0	0.57	30.7	31.5
8000.0	0.60	33.9	35.1
8500.0	0.61	38.8	37.2
9000.0	0.62	34.9	33.4
9500.0	0.64	44.6	38.0
10000.0	0.64	34.8	29.6
10500.0	0.68	32.1	29.4
11000.0	0.68	31.3	29.2
11500.0	0.71	28.0	29.3
12000.0	0.71	29.3	32.4
12500.0	0.80	29.5	31.9
13000.0	0.78	32.3	29.4
13500.0	0.85	26.3	31.5
14000.0	0.88	30.2	29.4
14500.0	0.81	26.0	25.6
15000.0	0.90	24.9	24.6
15500.0	0.90	22.9	21.7
16000.0	0.93	21.3	20.4
16500.0	0.89	32.9	29.2
17000.0	0.91	30.5	24.1
17500.0	0.96	33.0	30.2
18000.0	0.97	26.3	26.5