

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
10.0	0.02	52.65	51.82
50.0	0.02	53.22	53.13
100.0	0.02	52.33	54.19
200.0	0.03	47.70	48.91
300.0	0.04	45.69	47.48
400.0	0.05	45.21	51.32
500.0	0.05	46.03	57.13
600.0	0.06	46.06	50.75
700.0	0.06	44.11	44.66
800.0	0.07	41.46	41.22
900.0	0.07	39.73	40.08
1000.0	0.08	39.25	40.21
1100.0	0.09	40.41	43.34
1250.0	0.09	43.73	53.10
1500.0	0.10	35.10	35.00
1750.0	0.11	35.31	35.13
2000.0	0.12	42.47	46.87
2250.0	0.13	32.66	32.56
2500.0	0.13	33.90	33.85
2750.0	0.14	43.56	47.86
3000.0	0.15	30.64	30.75
3250.0	0.15	30.92	30.97
3500.0	0.16	45.22	45.55
3750.0	0.16	28.90	28.93
4000.0	0.16	30.17	30.34
4250.0	0.17	43.37	46.50
4500.0	0.17	31.38	31.27
4750.0	0.18	30.01	29.91
5000.0	0.18	38.51	42.53
5250.0	0.19	32.62	33.48
5500.0	0.19	34.67	33.23
5750.0	0.19	39.93	42.64
6000.0	0.20	37.81	39.26
6250.0	0.20	39.99	38.58
6500.0	0.20	43.38	40.07
6750.0	0.20	40.47	39.62
7000.0	0.21	45.37	51.54
7250.0	0.21	33.45	33.73
7500.0	0.22	31.90	31.73
7750.0	0.22	42.29	47.47
8000.0	0.23	31.85	32.02
8250.0	0.23	32.61	31.98
8500.0	0.23	39.85	39.48
8750.0	0.25	26.26	26.27
9000.0	0.25	26.78	26.81
9250.0	0.25	36.05	35.85
9500.0	0.26	26.46	26.46
9750.0	0.26	27.18	27.52
10000.0	0.26	32.51	38.17
11000.0	0.27	30.40	29.06
12000.0	0.30	31.61	32.49
13000.0	0.33	25.13	25.49
14000.0	0.32	26.67	26.76
15000.0	0.32	25.77	27.52
16000.0	0.35	28.35	27.02
17000.0	0.31	24.02	23.99
18000.0	0.31	25.05	29.42