

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
10.0	0.01	52.86	52.98
100.0	0.04	45.35	45.54
250.0	0.06	47.02	49.96
500.0	0.10	50.71	45.93
750.0	0.12	40.37	39.46
1000.0	0.14	41.30	44.66
1500.0	0.19	34.13	33.79
2000.0	0.22	42.72	42.56
2500.0	0.25	31.66	31.82
3000.0	0.28	33.52	31.15
3500.0	0.31	37.25	37.57
4000.0	0.36	27.88	25.44
4500.0	0.42	29.78	26.18
5000.0	0.49	40.75	28.12
5500.0	0.58	31.87	24.25
6000.0	0.57	37.76	31.91
6500.0	0.50	51.45	33.01
7000.0	0.48	40.38	34.20
7500.0	0.54	28.66	29.91
8000.0	0.57	39.91	48.66
8500.0	0.53	24.70	26.16
9000.0	0.53	23.08	23.60
9500.0	0.52	42.74	44.49
10000.0	0.54	22.62	23.40
10500.0	0.58	26.12	27.77
11000.0	0.72	23.37	24.04
11500.0	0.76	22.07	22.38
12000.0	0.80	38.45	29.07
12500.0	0.76	19.46	23.74
13000.0	0.68	24.56	31.56
13500.0	0.70	22.91	26.43
14000.0	0.69	20.08	21.37
14500.0	0.63	27.86	29.07
15000.0	0.65	25.61	27.45
15500.0	0.66	27.13	29.18
16000.0	0.65	28.71	34.87
16500.0	0.73	24.82	27.94
17000.0	0.77	30.10	29.94
17500.0	0.77	20.01	20.39
18000.0	0.64	26.08	30.13