

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
100.0	0.02	37.6	38.5
200.0	0.03	32.8	33.6
300.0	0.04	31.1	31.7
500.0	0.06	38.4	38.8
600.0	0.07	45.0	46.8
800.0	0.09	31.7	31.7
900.0	0.09	31.0	31.0
1000.0	0.09	33.3	33.1
1200.0	0.10	39.7	42.1
1400.0	0.10	30.8	32.5
1600.0	0.10	34.4	33.5
1800.0	0.10	33.0	36.4
2000.0	0.12	29.8	30.5
2200.0	0.13	31.1	31.0
2400.0	0.14	30.6	31.5
2600.0	0.15	32.4	31.9
2800.0	0.17	32.6	33.3
3000.0	0.18	30.0	30.6
3500.0	0.20	28.1	29.4
4000.0	0.22	30.0	32.6
4500.0	0.23	31.5	33.2
5000.0	0.27	31.2	30.9
5500.0	0.29	31.3	28.5
6000.0	0.30	29.5	26.4
6500.0	0.31	36.2	33.4
7000.0	0.33	38.3	40.6
7500.0	0.34	35.3	37.0
8000.0	0.34	34.0	35.9
8500.0	0.36	32.4	31.1
9000.0	0.42	33.9	31.8
9500.0	0.38	30.1	30.6
10000.0	0.42	25.7	25.9
10500.0	0.43	27.1	28.1
11000.0	0.49	29.3	30.4
11500.0	0.50	25.2	25.6
12000.0	0.42	29.3	29.8
12500.0	0.47	25.6	26.0
13000.0	0.46	24.4	24.4
13500.0	0.45	25.5	24.6
14000.0	0.49	30.0	30.3
14500.0	0.57	26.0	26.9
15000.0	0.44	21.4	27.9
16000.0	0.41	21.8	24.6
16500.0	0.55	24.4	26.4
17500.0	0.67	24.7	25.8
18000.0	0.69	19.3	22.4