

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	VSWR (:1)
1000	65.98	157.93
1500	62.38	868.59
1600	61.00	1737.18
3800	55.64	1737.18
5000	53.71	133.63
6000	51.28	144.77
6500	51.25	193.02
9000	51.86	91.43
9760	50.32	34.75
10000	47.72	27.59
11000	28.02	11.31
11200	22.02	9.38
11800	4.84	1.53
12000	4.31	2.00
12100	4.46	2.07
12300	4.03	1.88
12400	4.07	1.77
12600	3.81	1.73
13000	3.90	1.75
13200	4.01	1.28
13600	5.50	1.86
14000	17.18	6.28
15000	49.12	9.13
15170	53.19	9.90
16000	49.83	18.70
17000	43.66	72.39
17200	42.65	144.77
19000	37.28	78.97
20000	35.36	59.91
21000	34.26	144.77
22000	35.47	82.73
22500	34.94	347.44
25000	29.53	59.91
26000	28.03	57.91
27000	26.51	91.43
28000	25.60	52.65
29000	23.24	248.17
30000	23.23	24.83
31000	21.44	8.43
32000	18.59	6.97
33000	22.68	11.46
34000	23.59	7.56
35000	23.89	2.73
36000	30.91	3.34
37000	31.10	10.89
38000	17.23	20.22
39000	9.48	5.81
40000	7.75	7.44