

# Test Cable, N-Male/N-Male

# CBL-20FT-NMNM+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
1	0.05	44.30	44.11
100	0.57	44.39	43.60
500	1.70	38.92	38.21
1000	2.02	38.16	37.15
1500	2.82	34.67	34.98
2000	3.31	34.69	35.98
2500	3.75	34.86	36.60
3000	4.16	38.32	37.66
3500	4.55	41.14	37.66
4000	4.92	43.63	40.50
4500	5.27	41.83	40.57
5000	5.59	39.55	42.30
5500	5.91	36.08	42.30
6000	6.23	35.65	48.53
6500	6.54	35.45	49.21
7000	6.86	37.40	49.36
7500	7.17	37.80	45.15
8000	7.47	37.03	43.19
8500	7.73	34.44	40.57
9000	7.97	32.46	37.57
9500	8.18	30.76	37.92
10000	8.40	29.74	37.72
10500	8.61	28.80	37.77
11000	8.84	27.98	36.61
11500	9.10	27.38	35.94
12000	9.35	26.51	34.14
12500	9.60	26.21	30.84
13000	9.85	25.69	27.46
13500	10.10	25.75	25.43
14000	10.39	25.05	24.48
14500	10.65	24.52	23.88
15000	10.85	23.52	23.69
15500	11.07	23.50	23.98
16000	11.28	24.52	24.33
16500	11.52	26.68	25.40
17000	11.73	28.91	26.75
17500	11.92	29.45	28.05
18000	12.10	27.72	28.20

REV. X1  
CBL-20FT-NMNM+  
061115  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

