

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
2000	36.30	97.37	53.38
2400	35.88	93.53	62.82
2800	36.64	101.80	72.51
3200	40.67	113.86	66.77
3500	55.21	104.57	60.58
3600	50.65	93.06	58.74
4000	51.38	41.74	34.86
4400	7.81	5.15	4.92
4800	1.30	1.30	1.28
4900	1.15	1.24	1.19
4950	1.08	1.19	1.13
5000	1.03	1.15	1.07
5050	0.99	1.14	1.03
5100	0.96	1.14	1.06
5150	0.93	1.17	1.11
5200	0.92	1.21	1.16
5250	0.91	1.24	1.21
5300	0.90	1.28	1.25
5350	0.89	1.31	1.29
5400	0.88	1.33	1.32
5450	0.88	1.35	1.33
5500	0.87	1.35	1.34
5550	0.86	1.34	1.34
5600	0.85	1.33	1.32
5650	0.84	1.30	1.29
5700	0.83	1.27	1.26
5750	0.82	1.22	1.21
5800	0.81	1.17	1.16
5850	0.81	1.12	1.11
5900	0.82	1.09	1.08
5920	0.83	1.10	1.09
6000	0.90	1.22	1.21
6500	3.74	4.81	4.59
7000	9.99	21.26	17.48
7500	15.95	55.80	37.03
8000	20.71	80.91	49.22
8500	23.59	92.44	54.22
9000	25.41	107.53	57.37
9500	26.95	125.87	66.92
9800	28.19	124.41	69.37
10000	28.76	126.10	74.37
10200	29.25	131.03	68.57
10400	29.89	141.70	68.26
10600	30.74	135.76	65.28
10800	31.74	126.23	60.17
11000	32.84	115.63	56.35
11200	34.01	99.01	52.58
11400	35.36	84.21	48.87
11600	37.07	71.43	42.94
11800	39.51	60.76	37.99
11840	40.13	59.03	37.40
12000	43.38	52.34	33.89
12500	50.27	42.33	27.30
13000	41.76	43.18	27.25
13500	41.07	49.68	30.40
14000	41.14	60.10	33.69
14500	40.05	73.12	36.50
14700	38.82	77.89	37.27
15000	37.77	83.42	38.54
15500	35.66	88.24	42.81
16000	33.28	91.79	46.35
16500	31.38	88.56	54.95
17000	25.82	29.04	39.29
17500	14.27	7.28	10.77
17760	11.93	8.14	4.13
18000	8.81	3.71	2.58

