

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
100	0.07	43.5	45.9
200	0.10	39.6	40.4
300	0.14	40.1	39.5
400	0.16	43.3	47.0
500	0.17	46.7	42.5
600	0.19	40.2	39.1
700	0.20	40.6	41.2
800	0.22	45.3	49.7
900	0.23	41.9	40.2
1000	0.23	38.4	38.3
1100	0.25	41.1	42.6
1250	0.27	45.8	43.4
1500	0.29	48.4	54.8
1750	0.31	42.0	44.7
2000	0.33	45.5	45.9
2001	0.33	45.7	46.2
2250	0.34	44.4	43.9
2500	0.37	38.8	39.4
2750	0.39	38.2	38.9
3000	0.41	43.0	38.0
3250	0.42	32.7	30.0
3500	0.45	30.6	28.4
3750	0.47	40.6	43.2
4000	0.49	34.5	29.6
4250	0.51	29.5	26.1
4500	0.53	31.9	30.1
5000	0.55	32.3	28.2
5500	0.56	33.9	33.7
6000	0.59	26.9	25.7
6500	0.60	30.6	39.1
7000	0.64	21.0	23.2
7500	0.66	29.7	37.9
8000	0.67	23.5	24.7
8500	0.68	33.3	33.7
9000	0.66	26.9	28.0
9500	0.70	22.3	24.7
10000	0.67	24.6	22.5
10500	0.72	23.9	22.0
11000	0.74	25.0	24.1
11500	0.75	26.8	21.7
12000	0.75	30.8	35.9
12500	0.77	26.2	21.2
13000	0.80	36.7	49.7
13500	0.77	25.5	23.6
14000	0.80	33.2	26.1
14500	0.81	27.6	25.6
15000	0.82	32.6	24.9
15500	0.83	30.0	24.0
16000	0.80	30.0	48.4
16500	0.79	35.0	31.0
17000	0.90	21.9	21.7
17500	0.87	31.7	38.3
18000	0.95	21.8	22.4