

Fixed Attenuator

BW-40N250W+

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)	
		N-Male	N-Female
10	40.18	1.03	1.01
100	40.25	1.03	1.02
500	40.33	1.03	1.03
1000	40.36	1.03	1.05
1200	40.37	1.04	1.06
1400	40.39	1.05	1.06
1600	40.41	1.06	1.06
1800	40.41	1.06	1.07
2000	40.41	1.06	1.07
2200	40.41	1.06	1.07
2400	40.41	1.07	1.07
2600	40.41	1.05	1.07
2800	40.40	1.05	1.08
3000	40.40	1.09	1.09
3200	40.39	1.07	1.10
3400	40.37	1.10	1.11
3600	40.35	1.15	1.13
3800	40.34	1.18	1.14
4000	40.31	1.19	1.16
4200	40.27	1.21	1.17
4400	40.22	1.20	1.18
4600	40.17	1.13	1.19
4800	40.12	1.12	1.19
5000	40.09	1.14	1.18
5200	40.04	1.11	1.18
5400	39.98	1.11	1.16
5600	39.92	1.09	1.14
5800	39.86	1.04	1.12
6000	39.81	1.05	1.09
6200	39.75	1.10	1.07
6400	39.70	1.09	1.06
6600	39.61	1.05	1.06
6800	39.56	1.07	1.07
7000	39.49	1.07	1.08
7200	39.41	1.07	1.09
7400	39.32	1.07	1.10
7600	39.24	1.09	1.10
7800	39.14	1.08	1.10
8000	39.08	1.08	1.10