

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
100	0.12	39.5	41.2
200	0.17	55.7	48.6
300	0.21	40.2	40.9
400	0.24	50.3	46.6
500	0.27	39.7	40.7
600	0.30	48.9	43.7
700	0.32	39.7	39.8
800	0.34	46.5	45.0
900	0.36	41.7	40.6
1000	0.38	44.6	43.1
1100	0.41	43.4	41.0
1250	0.43	41.9	41.8
1500	0.47	48.6	41.7
1750	0.51	46.4	55.6
2000	0.54	40.1	41.0
2001	0.54	40.1	40.9
2250	0.57	42.9	38.6
2500	0.61	45.2	43.6
2750	0.64	41.0	44.2
3000	0.66	39.1	37.2
3250	0.69	38.6	39.5
3500	0.72	37.5	40.6
3750	0.74	33.5	32.4
4000	0.76	38.8	38.1
4250	0.81	32.8	33.9
4500	0.83	31.8	30.5
5000	0.87	29.0	29.6
5500	0.91	32.5	33.1
6000	0.94	39.8	44.8
6500	1.06	25.9	26.6
7000	1.09	24.3	23.7
7500	1.09	27.1	26.5
8000	1.12	31.6	34.1
8500	1.16	23.4	23.1
9000	1.24	21.6	21.7
9500	1.24	24.6	25.3
10000	1.25	39.3	34.5
10500	1.25	22.0	22.9
11000	1.40	25.7	25.0
11500	1.36	34.9	29.6
12000	1.36	31.5	31.5
12500	1.41	28.6	28.3
13000	1.42	43.0	41.6
13500	1.45	32.1	37.1
14000	1.48	29.9	40.1
14500	1.54	36.2	39.7
15000	1.54	25.7	26.3
15500	1.57	25.5	24.4
16000	1.60	35.8	37.4
16500	1.68	30.4	26.7
17000	1.66	26.1	28.4
17500	1.72	44.6	29.1
18000	1.72	37.9	40.7

