

# Test Cable, N-Male/N-Male

# CBL-1.5M-NMNM+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
0.3	0.01	51.64	54.23
0.7	0.02	51.53	51.61
1.0	0.02	50.46	50.51
3.0	0.03	47.02	47.04
5.0	0.04	45.45	45.44
7.0	0.04	44.50	44.39
9.0	0.05	43.78	43.64
10.0	0.05	43.15	43.33
30.0	0.10	40.32	39.35
50.0	0.13	40.82	39.93
70.0	0.15	46.63	48.74
90.0	0.17	43.77	42.76
100.0	0.18	40.43	39.27
200.0	0.26	37.05	37.07
300.0	0.32	46.87	47.46
400.0	0.37	35.44	34.72
500.0	0.42	33.01	33.08
600.0	0.46	42.18	43.29
700.0	0.50	31.44	32.31
800.0	0.53	35.70	36.50
900.0	0.57	32.93	36.01
1000.0	0.60	30.19	30.46
1500.0	0.74	29.01	29.11
2000.0	0.88	27.13	26.88
2500.0	0.97	27.08	26.41
3000.0	1.10	27.34	26.19
3500.0	1.19	29.57	27.11
4000.0	1.29	33.36	27.81
4500.0	1.40	32.09	26.46
5000.0	1.47	30.84	26.51
5500.0	1.56	32.16	27.03
6000.0	1.64	32.31	29.39
6500.0	1.73	31.84	29.96
7000.0	1.83	30.47	28.45
7500.0	1.94	29.28	29.67
8000.0	2.04	30.51	24.55
8500.0	2.16	30.21	24.03
9000.0	2.28	30.26	23.12
9500.0	2.25	38.99	32.10
10000.0	2.22	38.53	26.39
11000.0	2.31	25.41	21.97
11500.0	2.37	26.94	25.50
12000.0	2.40	27.50	24.45
13000.0	2.56	26.12	25.15
14000.0	2.91	28.32	22.68
15000.0	2.83	38.09	29.83
16000.0	2.99	25.50	34.93
17000.0	3.25	26.09	31.79
18000.0	3.27	31.35	23.36