

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
100	0.11	42.5	41.6
200	0.17	54.1	51.4
300	0.21	49.3	46.3
400	0.25	51.6	44.5
500	0.28	48.4	48.7
600	0.31	54.9	45.7
700	0.33	46.2	47.4
800	0.36	44.4	51.6
900	0.38	44.4	42.8
1000	0.41	44.0	44.6
1100	0.42	40.6	44.9
1250	0.45	43.4	45.7
1500	0.49	39.1	39.6
1750	0.53	51.1	52.3
2000	0.57	36.5	38.4
2001	0.57	36.4	38.4
2250	0.60	42.3	45.5
2500	0.64	33.0	34.9
2750	0.68	43.7	40.6
3000	0.72	32.1	32.3
3250	0.74	38.8	38.0
3500	0.78	32.4	30.5
3750	0.82	31.9	30.1
4000	0.83	39.8	34.7
4250	0.87	30.3	28.7
4500	0.90	41.8	40.6
5000	0.95	33.4	35.1
5500	1.02	34.2	31.6
6000	1.08	33.0	30.0
6500	1.11	28.3	27.7
7000	1.14	25.9	28.2
7500	1.20	22.9	26.7
8000	1.21	24.9	26.7
8500	1.25	28.7	26.3
9000	1.23	24.4	31.2
9500	1.30	22.8	41.8
10000	1.29	23.3	30.1
10500	1.38	21.3	21.8
11000	1.43	20.7	19.2
11500	1.44	21.9	19.7
12000	1.47	23.3	21.1
12500	1.48	24.0	22.8
13000	1.45	55.0	26.4
13500	1.50	48.8	29.7
14000	1.53	24.4	27.5
14500	1.53	23.4	31.9
15000	1.58	22.6	28.3
15500	1.60	20.4	36.4
16000	1.61	23.7	25.5
16500	1.62	21.0	21.7
17000	1.70	21.1	22.3
17500	1.75	21.9	22.1
18000	1.83	25.2	28.4