

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
100	0.04	31.8	31.9
200	0.06	28.6	28.2
300	0.07	30.9	30.8
400	0.08	48.3	50.3
500	0.09	32.3	32.1
600	0.11	28.5	28.4
700	0.10	30.5	30.5
800	0.11	44.4	45.3
900	0.13	33.2	33.1
1000	0.13	29.0	29.0
1100	0.14	31.0	31.1
1250	0.14	39.3	39.3
1500	0.15	31.5	31.9
1750	0.19	30.4	31.0
2000	0.17	45.0	45.4
2001	0.17	45.2	45.8
2250	0.17	31.2	31.6
2500	0.20	34.5	35.9
2750	0.20	39.9	40.0
3000	0.20	31.8	34.5
3250	0.22	37.7	37.6
3500	0.22	34.7	37.9
3750	0.23	33.4	36.7
4000	0.24	46.6	37.5
4250	0.25	34.9	42.3
4500	0.23	32.8	33.4
5000	0.26	32.5	38.0
5500	0.26	33.4	33.6
6000	0.32	31.3	29.3
6500	0.29	32.1	31.4
7000	0.32	29.0	29.8
7500	0.31	26.1	25.6
8000	0.32	31.1	28.0
8500	0.35	27.1	27.2
9000	0.39	22.3	22.7
9500	0.34	28.9	29.4
10000	0.39	26.5	25.1
10500	0.38	22.2	22.2
11000	0.39	26.2	29.2
11500	0.44	26.6	25.6
12000	0.45	22.8	22.1
12500	0.37	28.2	30.1
13000	0.41	27.4	27.6
13500	0.42	23.1	25.2
14000	0.39	23.4	34.9
14500	0.39	26.5	28.6
15000	0.42	28.2	30.5
15500	0.43	22.7	38.3
16000	0.42	21.5	35.9
16500	0.45	28.0	32.0
17000	0.43	30.8	32.0
17500	0.55	23.0	31.1
18000	0.57	22.7	31.9