

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100	0.03	31.5	31.6
200	0.05	28.7	28.6
300	0.05	33.2	33.2
400	0.06	39.9	41.6
500	0.07	29.0	29.8
600	0.09	28.6	28.9
700	0.09	36.8	35.4
800	0.10	33.8	36.0
900	0.11	27.3	28.2
1000	0.12	29.1	28.6
1100	0.12	49.2	43.0
1250	0.14	27.1	27.2
1500	0.15	35.2	36.9
1750	0.17	32.4	31.7
2000	0.18	27.3	27.2
2001	0.18	27.3	27.2
2250	0.19	30.6	30.9
2500	0.20	44.1	40.6
2750	0.21	33.7	31.3
3000	0.23	31.9	31.7
3250	0.23	35.5	37.4
3500	0.24	42.9	37.4
3750	0.26	40.0	37.1
4000	0.25	42.6	40.3
4250	0.26	33.2	33.2
4500	0.29	32.6	31.7
5000	0.31	30.1	31.4
5500	0.33	28.6	29.1
6000	0.37	27.0	26.9
6500	0.37	26.3	26.0
7000	0.38	24.9	24.9
7500	0.40	26.1	26.6
8000	0.42	24.7	24.1
8500	0.42	31.5	30.2
9000	0.43	26.6	24.5
9500	0.45	30.7	35.7
10000	0.48	26.0	23.6
10500	0.48	24.4	26.3
11000	0.48	33.6	28.4
11500	0.51	23.8	24.0
12000	0.52	28.0	28.5
12500	0.55	25.2	26.2
13000	0.49	27.7	25.3
13500	0.57	40.8	32.1
14000	0.57	25.2	31.5
14500	0.56	30.3	42.9
15000	0.59	37.2	29.3
15500	0.60	24.5	32.5
16500	0.60	32.3	33.8
17000	0.61	26.7	27.2
17500	0.67	29.5	27.2
18000	0.72	29.0	28.8