

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100	0.07	41.1	42.1
200	0.10	36.7	38.1
300	0.11	39.3	39.5
400	0.13	53.2	51.5
500	0.14	38.1	38.6
600	0.16	35.5	35.8
700	0.18	39.9	40.0
800	0.19	41.1	45.2
900	0.20	34.6	34.8
1000	0.21	35.0	34.8
1100	0.22	45.7	45.7
1250	0.24	35.1	34.8
1500	0.26	42.6	43.2
1750	0.28	42.3	43.5
2000	0.30	36.6	35.6
2001	0.30	36.6	35.6
2250	0.31	37.3	35.8
2500	0.33	40.8	40.1
2750	0.35	50.3	44.4
3000	0.36	39.3	35.9
3250	0.38	34.6	32.1
3500	0.40	34.1	32.2
3750	0.41	35.5	34.7
4000	0.42	37.6	33.9
4250	0.44	32.9	29.9
4500	0.46	31.8	29.6
5000	0.48	35.1	33.1
5500	0.50	31.8	30.5
6000	0.53	34.0	32.9
6500	0.55	31.2	30.4
7000	0.57	34.1	33.6
7500	0.60	28.7	28.3
8000	0.62	39.0	35.4
8500	0.65	28.3	28.0
9000	0.67	41.0	40.3
9500	0.69	26.1	25.7
10000	0.70	35.8	46.5
10500	0.72	26.2	26.6
11000	0.72	31.9	36.2
11500	0.76	26.3	26.7
12000	0.78	26.8	27.7
12500	0.80	26.6	25.9
13000	0.84	22.6	22.5
13500	0.83	30.3	27.6
14000	0.87	22.4	21.8
14500	0.87	30.1	25.7
15000	0.91	22.8	21.8
15500	0.91	31.2	28.1
16000	0.93	25.9	24.8
16500	0.94	34.3	30.1
17000	0.96	26.8	26.0
17500	0.96	37.9	34.5
18000	1.00	25.9	24.3