

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
100	0.08	28.9	29.5
200	0.11	40.4	39.6
300	0.13	30.0	30.3
400	0.14	34.6	34.5
500	0.17	31.4	31.4
600	0.18	31.8	31.5
700	0.19	34.2	34.1
800	0.21	30.1	29.6
900	0.21	39.4	39.2
1000	0.24	29.7	28.9
1100	0.24	50.0	54.2
1250	0.26	34.6	35.3
1500	0.28	34.9	32.4
1750	0.30	31.1	29.4
2000	0.32	45.5	56.4
2001	0.32	47.4	57.2
2250	0.31	32.4	29.0
2500	0.39	33.9	30.8
2750	0.37	45.4	40.6
3000	0.41	33.2	28.5
3250	0.41	46.9	40.1
3500	0.43	35.2	30.6
3750	0.43	37.0	30.3
4000	0.44	42.3	41.2
4250	0.48	37.2	29.6
4500	0.47	44.2	40.3
5000	0.50	40.1	31.6
5500	0.51	35.0	31.2
6000	0.57	35.5	33.3
6500	0.61	34.9	35.9
7000	0.64	27.8	33.3
7500	0.64	25.5	30.6
8000	0.65	29.3	29.4
8500	0.68	34.5	30.8
9000	0.73	24.8	32.9
9500	0.76	21.3	26.7
10000	0.83	20.8	23.6
10500	0.82	27.6	22.7
11000	0.80	27.3	23.8
11500	0.88	27.7	22.8
12000	0.89	22.6	22.2
12500	0.89	22.7	23.0
13000	0.90	28.8	24.6
13500	0.95	28.1	25.3
14000	1.00	29.0	26.2
14500	0.84	24.5	28.8
15000	0.97	21.3	40.7
15500	0.97	27.2	29.2
16000	1.03	28.4	24.9
16500	0.97	24.9	25.7
17000	1.03	28.5	30.3
17500	1.05	28.1	34.6
18000	1.15	24.5	39.9

