

Voltage Controlled Oscillator

JTOS-150P+

Typical Performance Data

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ OFFSET (KHz)	PHASE NOISE (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C	F2	F3	F4			
0.5	9.99	67.2	64.7	63.3	8.59	8.46	8.11	-24.4	-30.3	-46.1		1	-82
1.0	8.82	71.0	69.2	68.3	9.43	9.62	9.45	-25.5	-32.0	-48.1	0.04	10	-106
1.5	7.70	74.5	73.2	72.4	9.95	10.36	10.19	-25.4	-33.4	-47.7		100	-127
2.0	7.36	78.1	76.9	76.2	9.95	10.30	10.11	-25.2	-34.5	-45.0	0.37	1000	-147
2.5	7.32	81.9	80.5	79.8	9.93	10.19	9.97	-25.7	-34.9	-42.9			
3.0	7.12	85.5	84.2	83.4	9.89	10.12	9.88	-26.2	-35.3	-42.3	0.23		
3.5	6.61	88.8	87.5	86.8	9.83	10.03	9.79	-26.4	-35.2	-41.6			
4.0	6.36	92.0	90.8	90.0	9.75	9.95	9.68	-26.7	-35.0	-41.0	0.17		
4.5	6.24	95.0	93.9	93.1	9.69	9.84	9.57	-26.9	-34.7	-40.6			
5.0	6.18	98.1	97.0	96.2	9.61	9.76	9.49	-27.1	-34.1	-40.1	0.16		

REV. X1
 JTOS-150P+
 070131
 Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

