


















Typical Performance Curves











Typical Performance Curves

$I_{DS} = 15 \text{ mA}$



Typical Performance Curves

$I_{DS} = 30 \text{ mA}$



Typical Performance Curves

$I_{DS} = 60 \text{ mA}$

