

Typical Performance Data

FREQUENCY	INSERTION LOSS	RETURN LOSS
(MHz)	(dB)	(dB)
0.3	71.30	0.00
0.7	63.13	0.00
1.0	60.17	0.00
3.0	50.57	0.00
7.0	43.28	0.00
10.0	40.24	0.00
100.0	26.58	0.07
700.0	50.05	0.19
1000.0	38.43	0.22
1400.0	39.59	0.27
1500.0	47.76	0.30
1550.0	48.98	0.32
1600.0	39.40	0.35
1700.0	28.65	0.44
1800.0	20.92	0.61
1900.0	13.87	1.11
2000.0	7.18	2.99
2100.0	2.73	10.79
2170.0	1.80	20.11
2175.0	1.77	19.96
2180.0	1.75	19.71
2190.0	1.71	19.01
2200.0	1.68	18.29
2210.0	1.65	17.65
2220.0	1.63	17.16
2230.0	1.61	16.82
2240.0	1.60	16.63
2250.0	1.58	16.59
2260.0	1.56	16.68
2270.0	1.55	16.90
2280.0	1.54	17.27
2290.0	1.52	17.79
2300.0	1.51	18.47
2310.0	1.50	19.33
2320.0	1.49	20.37
2330.0	1.49	21.52
2340.0	1.49	22.68
2350.0	1.50	23.37
2360.0	1.51	23.14
2370.0	1.53	21.95
2380.0	1.56	20.23
3400.0	19.75	0.36
3500.0	21.07	0.34
3700.0	23.66	0.33
3900.0	26.37	0.33
4000.0	27.86	0.34
4200.0	30.98	0.34
4400.0	34.86	0.34
4600.0	40.54	0.35
4800.0	52.61	0.36
5000.0	47.67	0.38
5200.0	40.52	0.39
5400.0	37.78	0.42
5600.0	36.84	0.42
5800.0	37.75	0.45
6000.0	34.26	0.57