

Coaxial SMA Band Pass Filter

VBFZ-6260-S+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
50	61.42	0.01
1500	35.70	0.12
2500	38.25	0.23
4100	31.23	0.45
4200	33.45	0.43
4600	18.69	0.94
4800	8.89	2.20
4950	4.26	5.36
5100	2.18	11.01
5600	1.22	25.80
6260	1.20	14.80
7000	1.27	15.84
8000	2.35	15.42
8200	4.54	7.92
8350	8.83	4.18
8500	15.54	2.48
8750	31.12	1.57
9300	36.77	1.12
14000	37.83	3.69
18000	34.51	3.05

REV. OR
VBFZ-6260-S+
200811
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

