

Plug-In Band Pass Filter (Constant Impedance) PIF-30+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	30.97	59.50	5.3	4.911
1.2	29.52	57.90	7.0	5.392
1.4	28.29	57.10	8.0	5.612
1.5	27.23	56.50	12.0	6.685
1.7	26.25	56.00	16.0	8.448
1.9	25.40	55.50	20.0	10.612
2.0	24.95	55.80	21.0	11.190
5.3	16.33	49.50	25.0	12.864
7.0	13.88	47.50	26.0	13.075
8.0	12.64	46.00	27.3	13.145
12.0	8.66	41.60	28.8	12.980
16.0	5.59	37.40	30.0	12.639
20.0	3.10	33.50	31.0	12.237
26.0	0.66	29.60	32.3	11.647
28.7	0.26	28.00	33.8	10.775
31.0	0.25	26.70	35.0	10.047
33.7	0.55	26.10	36.0	9.449
44.0	2.99	27.10	44.0	5.471
45.0	3.25	27.20	45.0	5.093
70.0	8.33	30.40	70.0	1.581
95.0	11.72	31.50	95.0	0.883
120.0	14.33	31.80	120.0	0.718
121.0	14.43	31.80	121.0	0.703
180.0	19.47	31.20	150.8	0.518
210.0	21.85	30.80	180.3	0.428
211.0	21.93	30.80	210.0	0.305
258.6	26.09	29.80	233.8	0.196
282.4	28.52	29.30	234.0	0.244
306.2	31.23	28.70	258.0	0.031
330.0	34.20	28.20	282.0	0.378

REV. X1
PIF-30+
060725
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

