

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10	12.03	1.17
50	12.02	1.16
100	12.02	1.16
200	12.03	1.16
300	12.04	1.16
400	12.05	1.15
500	12.06	1.15
1000	12.08	1.14
1500	12.08	1.13
2000	12.08	1.11
2500	12.07	1.09
3000	12.06	1.07
3500	12.06	1.05
4000	12.07	1.03
4500	12.07	1.01
5000	12.09	1.02
5500	12.09	1.06
6000	12.11	1.10
6500	12.12	1.13
7000	12.14	1.13
7500	12.14	1.13
8000	12.15	1.11
8500	12.15	1.09
9000	12.16	1.08
9500	12.16	1.08
10000	12.18	1.09
10500	12.19	1.11
11000	12.20	1.12
11500	12.20	1.13
12000	12.20	1.13
12500	12.21	1.13
13000	12.22	1.13
13500	12.23	1.15
14000	12.25	1.17
14500	12.26	1.20
15000	12.28	1.23
15500	12.30	1.25
16000	12.31	1.24
16500	12.30	1.23
17000	12.28	1.21
17500	12.26	1.18
18000	12.26	1.17