

Switch SP4T , 50W

ZSDR-425+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS TTL Low @ 0V (dB) IN-OUT , "ON"	ISOLATION TTL High @ 5V (dB) IN-OUT , "OFF"	VSWR		
			IN	(:1) OUT , "ON"	OUT , "OFF"
10.00	1.22	74.41	1.35	1.40	27.25
20.00	1.06	70.64	1.19	1.22	27.08
50.00	0.97	61.72	1.11	1.13	27.42
100.00	0.94	56.09	1.10	1.11	26.82
200.00	0.90	49.80	1.13	1.12	26.58
408.40	1.01	45.66	1.21	1.18	26.03
500.00	1.06	44.93	1.25	1.20	24.98
669.85	1.10	44.06	1.30	1.24	24.36
856.60	1.30	43.15	1.35	1.25	22.45
1000.00	1.39	44.52	1.37	1.24	20.59
1118.05	1.48	42.72	1.37	1.23	19.44
1250.00	1.37	42.75	1.36	1.22	19.15
1391.95	1.51	44.07	1.34	1.20	18.57
1578.70	1.47	40.41	1.31	1.16	17.15
1777.90	1.52	37.07	1.30	1.14	16.04
2002.00	1.66	34.27	1.30	1.16	13.88
2176.30	1.81	30.64	1.30	1.21	12.25
2363.05	1.82	26.86	1.28	1.28	9.41
2437.75	2.08	25.66	1.29	1.30	7.81
2500.00	2.14	25.03	1.30	1.31	7.10



ISO 9001 ISO 14001 AS 9100 CERTIFIED

For detailed performance specs & shopping online see web site

P.O. Box 350166, Brooklyn, New York 11235-0008 (718) 934-4500 Fax (718) 332-4661 The Design Engineers Search Engine Provides ACTUAL Data Instantly at minicircuits.com

RF/MICROWAVE COMPONENTS

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuits' applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"). Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCISHome/terms.jsp.