

SP2T Solid-State Switch

RCS-1SP2T-A673

Typical Performance Data

Test Conditions: @ Temperature = -10°C, Pin = 8 dBm.

Freq. (GHz)	Insertion Loss (dB)		Isolation, Active states (dB)			Isolation, Disconnected states (dB)		
	COM-1	COM-2	COM-1	COM-2	1-2	COM-1	COM-2	1-2
0.10	-0.70	-0.70	-90.52	-89.75	-95.29	-92.23	-92.74	-100.48
0.50	-0.79	-0.79	-80.26	-80.12	-87.38	-80.01	-77.70	-92.92
1.00	-0.86	-0.85	-74.39	-74.34	-80.96	-74.35	-71.12	-86.59
2.50	-1.02	-1.02	-67.15	-67.23	-73.16	-67.17	-64.09	-80.04
4.00	-1.12	-1.12	-63.76	-63.72	-70.94	-63.82	-61.06	-75.91
6.00	-1.24	-1.24	-61.69	-61.77	-69.31	-61.78	-59.30	-71.75
8.00	-1.37	-1.37	-60.81	-61.06	-71.29	-60.89	-58.75	-68.45
10.00	-1.45	-1.45	-59.51	-59.77	-70.95	-59.45	-58.50	-65.50
12.00	-1.63	-1.63	-56.66	-57.07	-65.70	-56.69	-56.71	-62.50
14.00	-1.75	-1.74	-53.50	-54.01	-58.88	-53.49	-53.95	-59.80
16.00	-1.94	-1.93	-52.15	-52.66	-56.96	-52.17	-52.77	-58.24
18.00	-2.17	-2.14	-52.20	-53.37	-54.03	-52.18	-54.05	-56.45
20.00	-2.23	-2.24	-54.68	-56.53	-53.31	-54.68	-57.13	-53.37
22.00	-2.33	-2.31	-52.81	-53.04	-49.80	-52.78	-57.79	-50.60
24.00	-2.67	-2.67	-50.52	-50.82	-49.03	-50.47	-59.92	-48.70
26.00	-2.62	-2.61	-48.65	-48.49	-46.63	-48.65	-59.18	-46.71
28.00	-2.79	-2.83	-45.62	-46.03	-46.08	-45.62	-53.26	-44.88
30.00	-2.88	-2.99	-47.74	-48.81	-45.74	-47.71	-50.25	-44.81
32.00	-2.88	-3.05	-48.06	-49.51	-47.76	-48.05	-50.16	-45.94
34.00	-3.16	-3.31	-47.62	-48.00	-48.57	-47.66	-49.06	-45.68
36.00	-3.11	-3.39	-48.07	-48.07	-45.53	-48.09	-48.78	-44.97
38.00	-3.72	-3.98	-46.74	-47.59	-42.68	-46.67	-47.96	-43.69
40.00	-3.50	-3.98	-46.39	-46.86	-43.76	-46.51	-47.63	-45.12
41.50	-3.90	-4.35	-49.26	-51.53	-48.53	-49.25	-49.08	-47.92
43.00	-3.90	-4.26	-49.82	-52.23	-52.36	-49.98	-51.62	-49.33
44.50	-3.98	-4.21	-49.13	-49.04	-52.96	-49.14	-52.31	-48.53
46.00	-3.82	-4.16	-46.02	-45.68	-48.99	-45.93	-51.24	-49.17
47.50	-4.81	-4.81	-48.01	-48.01	-49.91	-48.19	-50.01	-51.29
49.00	-4.57	-4.71	-47.21	-48.04	-51.34	-46.97	-48.97	-51.17
50.50	-4.17	-4.27	-46.50	-48.11	-49.68	-46.38	-47.53	-52.22
52.00	-4.66	-4.86	-48.63	-49.59	-50.59	-48.43	-46.69	-60.21
53.50	-4.72	-4.90	-47.62	-48.28	-51.40	-47.46	-45.38	-70.78
55.00	-5.37	-5.56	-43.84	-44.53	-51.45	-43.83	-42.60	-73.90
56.50	-4.72	-4.85	-44.64	-44.83	-48.24	-44.72	-41.71	-68.17
58.00	-5.10	-5.13	-43.93	-43.76	-46.55	-43.93	-42.37	-64.43
59.50	-4.98	-4.95	-42.22	-41.67	-44.87	-42.18	-43.91	-58.42
61.00	-5.74	-5.61	-43.18	-43.34	-43.39	-43.18	-46.23	-54.62
62.50	-6.17	-6.19	-45.51	-45.20	-43.03	-45.47	-48.66	-54.20
64.00	-6.41	-6.27	-41.43	-41.60	-43.50	-41.34	-47.44	-52.54
65.50	-7.46	-7.21	-43.96	-43.80	-46.04	-44.02	-44.81	-53.12
67.00	-6.89	-6.67	-44.91	-43.93	-46.59	-45.14	-44.27	-57.42

SP2T Solid-State Switch

RCS-1SP2T-A673

Typical Performance Data

Test Conditions: @ Temperature = -10°C, Pin = 8 dBm.

Freq. (GHz)	Return Loss, Active ports (dB)			RL, Terminated ports (dB)	
	COM	1	2	1	2
0.10	-22.58	-23.20	-23.22	-29.81	-29.84
0.50	-22.20	-22.19	-22.31	-31.41	-31.05
1.00	-23.12	-21.34	-21.82	-33.50	-32.05
2.50	-30.55	-19.81	-19.59	-40.13	-42.90
4.00	-22.91	-23.85	-22.73	-26.73	-26.77
6.00	-22.47	-26.99	-27.42	-27.40	-27.58
8.00	-24.22	-22.67	-21.73	-33.93	-35.75
10.00	-24.93	-23.87	-23.53	-25.12	-25.59
12.00	-22.19	-17.84	-17.54	-28.41	-31.07
14.00	-22.01	-19.74	-20.15	-26.72	-26.02
16.00	-17.54	-19.22	-19.18	-24.27	-29.12
18.00	-15.97	-15.92	-17.15	-26.05	-24.91
20.00	-19.48	-28.54	-22.96	-22.66	-23.39
22.00	-25.63	-20.86	-28.03	-17.91	-18.26
24.00	-15.91	-12.07	-11.98	-18.79	-20.08
26.00	-14.87	-18.56	-22.33	-16.32	-16.39
28.00	-17.75	-18.83	-18.81	-25.49	-23.79
30.00	-16.36	-18.74	-17.63	-18.07	-17.23
32.00	-16.43	-18.80	-17.27	-13.26	-12.77
34.00	-16.05	-12.72	-14.02	-25.11	-31.22
36.00	-20.40	-23.39	-22.57	-12.26	-12.56
38.00	-10.61	-11.48	-13.27	-12.74	-13.77
40.00	-15.21	-24.10	-27.08	-32.33	-33.22
41.50	-10.94	-10.72	-10.76	-10.38	-10.59
43.00	-18.23	-10.61	-11.15	-8.03	-8.65
44.50	-12.15	-10.46	-12.57	-13.85	-15.58
46.00	-17.92	-17.13	-17.72	-12.04	-13.30
47.50	-8.91	-7.98	-9.34	-7.59	-8.53
49.00	-10.34	-9.33	-9.74	-9.80	-10.19
50.50	-15.36	-14.63	-16.46	-19.35	-20.74
52.00	-10.64	-9.71	-9.50	-8.62	-9.11
53.50	-13.91	-11.32	-11.56	-7.84	-7.78
55.00	-8.03	-8.17	-8.02	-15.77	-15.25
56.50	-14.56	-21.42	-20.89	-12.63	-11.87
58.00	-11.24	-11.16	-11.49	-9.41	-10.00
59.50	-16.68	-12.03	-13.84	-12.21	-13.83
61.00	-11.71	-8.69	-10.13	-12.08	-14.59
62.50	-8.60	-8.03	-8.54	-6.54	-7.51
64.00	-8.91	-9.37	-11.53	-7.87	-8.79
65.50	-7.65	-5.38	-6.07	-9.36	-10.85
67.00	-27.57	-7.00	-7.55	-4.96	-5.31

SP2T Solid-State Switch

RCS-1SP2T-A673

Typical Performance Data

Test Conditions: @ Temperature = +25°C, Pin = 8 dBm.

Freq. (GHz)	Insertion Loss (dB)		Isolation, Active states (dB)			Isolation, Disconnected states (dB)		
	COM-1	COM-2	COM-1	COM-2	1-2	COM-1	COM-2	1-2
0.10	-0.78	-0.79	-90.45	-90.22	-96.39	-89.75	-90.98	-103.40
0.50	-0.88	-0.90	-79.58	-79.94	-84.40	-76.94	-76.93	-94.48
1.00	-0.96	-0.97	-73.61	-73.59	-79.17	-70.59	-70.84	-88.00
2.50	-1.15	-1.17	-66.37	-66.56	-72.09	-63.26	-63.17	-80.49
4.00	-1.25	-1.28	-63.09	-63.16	-69.11	-60.14	-60.06	-75.38
6.00	-1.39	-1.41	-60.88	-61.04	-67.26	-58.12	-58.11	-71.75
8.00	-1.52	-1.56	-59.99	-60.17	-68.20	-57.35	-57.39	-68.44
10.00	-1.61	-1.64	-58.89	-59.08	-68.43	-56.89	-57.04	-65.55
12.00	-1.81	-1.85	-56.50	-56.96	-65.35	-55.55	-55.88	-62.55
14.00	-1.94	-1.98	-53.50	-53.98	-58.74	-53.11	-53.67	-59.88
16.00	-2.15	-2.19	-52.18	-52.64	-56.55	-51.98	-52.49	-58.12
18.00	-2.37	-2.40	-52.04	-53.01	-53.43	-52.80	-53.42	-56.36
20.00	-2.46	-2.53	-54.21	-55.88	-52.39	-55.54	-56.15	-52.98
22.00	-2.58	-2.61	-53.54	-54.50	-48.70	-57.42	-57.71	-49.71
24.00	-2.92	-2.99	-51.31	-51.58	-48.04	-64.50	-60.28	-47.59
26.00	-2.90	-2.95	-49.26	-48.84	-45.84	-61.53	-60.49	-45.72
28.00	-3.07	-3.18	-46.32	-46.62	-45.50	-54.11	-54.40	-44.20
30.00	-3.17	-3.36	-47.98	-49.12	-45.95	-50.49	-50.97	-44.59
32.00	-3.16	-3.39	-48.07	-49.63	-48.45	-49.42	-50.15	-45.98
34.00	-3.45	-3.69	-48.01	-48.38	-49.16	-48.42	-49.01	-45.81
36.00	-3.46	-3.82	-48.54	-48.57	-45.79	-48.55	-48.73	-44.66
38.00	-4.06	-4.40	-47.41	-47.88	-43.04	-49.40	-48.09	-43.64
40.00	-3.87	-4.39	-47.64	-47.97	-44.67	-50.30	-47.72	-45.49
41.50	-4.34	-4.81	-50.82	-53.51	-48.79	-51.21	-49.09	-47.76
43.00	-4.25	-4.64	-50.67	-53.57	-51.85	-51.55	-51.13	-49.14
44.50	-4.34	-4.64	-49.35	-49.71	-52.08	-50.19	-51.84	-48.65
46.00	-4.24	-4.62	-46.54	-46.01	-48.73	-48.78	-51.20	-49.08
47.50	-5.24	-5.32	-48.32	-47.80	-49.68	-49.76	-50.24	-51.27
49.00	-4.94	-5.18	-47.17	-47.75	-50.98	-49.76	-49.20	-51.63
50.50	-4.68	-4.86	-46.61	-48.01	-49.53	-48.03	-47.84	-53.78
52.00	-5.04	-5.35	-48.49	-49.55	-49.82	-47.41	-46.75	-60.73
53.50	-5.22	-5.51	-47.05	-48.12	-51.13	-45.49	-45.23	-66.72
55.00	-5.76	-6.06	-43.74	-44.66	-50.76	-43.18	-42.68	-66.66
56.50	-5.26	-5.50	-45.12	-44.97	-48.08	-42.36	-41.63	-64.66
58.00	-5.55	-5.73	-44.23	-44.08	-46.36	-44.17	-42.47	-62.25
59.50	-5.37	-5.48	-42.77	-41.88	-45.05	-46.46	-44.04	-60.48
61.00	-6.09	-6.09	-44.06	-43.00	-43.27	-48.48	-45.54	-57.04
62.50	-6.74	-6.89	-46.28	-45.26	-42.92	-51.24	-48.23	-55.79
64.00	-7.18	-7.10	-42.19	-41.85	-43.32	-48.81	-47.31	-52.96
65.50	-7.66	-7.49	-44.35	-43.98	-45.11	-45.85	-44.96	-52.27
67.00	-7.45	-7.32	-45.17	-44.15	-45.18	-47.60	-45.66	-54.75

SP2T Solid-State Switch

RCS-1SP2T-A673

Typical Performance Data

Test Conditions: @ Temperature = +25°C, Pin = 8 dBm.

Freq. (GHz)	Return Loss, Active ports (dB)			RL, Terminated ports (dB)	
	COM	1	2	1	2
0.10	-21.69	-22.30	-22.24	-30.44	-30.46
0.50	-21.52	-21.44	-21.51	-32.21	-31.91
1.00	-22.29	-20.66	-21.03	-35.23	-33.49
2.50	-28.66	-19.28	-19.03	-39.06	-39.95
4.00	-22.77	-22.56	-21.47	-26.97	-26.78
6.00	-21.22	-26.68	-27.09	-27.85	-27.93
8.00	-23.35	-21.98	-21.10	-33.55	-34.17
10.00	-24.02	-23.37	-22.97	-25.10	-25.57
12.00	-22.48	-17.32	-16.96	-29.33	-32.22
14.00	-21.75	-19.70	-20.21	-25.98	-25.42
16.00	-16.96	-18.83	-18.91	-24.32	-29.41
18.00	-16.57	-16.44	-17.92	-28.05	-26.66
20.00	-18.76	-28.27	-22.94	-22.31	-23.55
22.00	-26.99	-20.29	-28.46	-18.55	-18.98
24.00	-16.34	-12.33	-12.27	-18.65	-20.30
26.00	-15.08	-18.82	-22.98	-16.96	-17.17
28.00	-17.66	-19.36	-19.41	-27.19	-24.92
30.00	-16.27	-18.50	-17.44	-17.58	-16.94
32.00	-18.02	-20.57	-18.95	-13.88	-13.39
34.00	-16.87	-13.30	-14.61	-26.67	-32.32
36.00	-19.37	-22.90	-22.21	-12.32	-12.71
38.00	-11.11	-11.75	-13.73	-13.15	-14.21
40.00	-15.50	-25.04	-29.12	-28.39	-34.13
41.50	-10.55	-10.45	-10.66	-10.17	-10.51
43.00	-22.43	-11.27	-12.03	-8.52	-9.13
44.50	-12.85	-10.82	-12.89	-14.85	-16.62
46.00	-19.10	-17.00	-18.15	-11.68	-13.00
47.50	-9.35	-8.11	-9.44	-7.88	-8.83
49.00	-11.27	-10.09	-10.56	-10.69	-11.07
50.50	-13.49	-14.19	-16.20	-19.09	-21.74
52.00	-11.94	-10.81	-10.60	-8.89	-9.45
53.50	-15.22	-11.26	-11.48	-8.64	-8.53
55.00	-8.98	-8.97	-8.86	-17.17	-16.32
56.50	-12.87	-23.34	-21.68	-12.67	-12.02
58.00	-10.89	-11.30	-11.79	-10.09	-10.73
59.50	-22.62	-13.26	-15.70	-13.70	-15.62
61.00	-13.92	-9.47	-11.13	-12.45	-15.30
62.50	-8.15	-8.32	-8.83	-6.76	-7.74
64.00	-7.81	-8.94	-10.89	-8.60	-9.64
65.50	-9.26	-6.30	-7.16	-9.73	-11.12
67.00	-20.22	-7.39	-8.12	-5.55	-5.94

SP2T Solid-State Switch

RCS-1SP2T-A673

Typical Performance Data

Test Conditions: @ Temperature = +60°C, Pin = 8 dBm.

Freq. (GHz)	Insertion Loss (dB)		Isolation, Active states (dB)			Isolation, Disconnected states (dB)		
	COM-1	COM-2	COM-1	COM-2	1-2	COM-1	COM-2	1-2
0.10	-0.85	-0.86	-92.35	-90.86	-97.55	-91.62	-87.64	-98.37
0.50	-0.96	-0.97	-79.46	-79.13	-84.11	-79.32	-76.27	-92.96
1.00	-1.04	-1.05	-72.94	-73.31	-78.40	-73.26	-69.95	-87.66
2.50	-1.24	-1.25	-65.93	-66.00	-71.56	-66.11	-62.47	-81.52
4.00	-1.36	-1.37	-62.57	-62.54	-68.43	-62.63	-59.36	-76.25
6.00	-1.51	-1.51	-60.18	-60.28	-66.38	-60.31	-57.24	-71.79
8.00	-1.65	-1.66	-59.35	-59.39	-66.88	-59.47	-56.36	-68.60
10.00	-1.75	-1.76	-58.28	-58.54	-66.48	-58.60	-55.97	-65.76
12.00	-1.96	-1.97	-56.22	-56.67	-64.37	-56.68	-55.13	-62.75
14.00	-2.10	-2.11	-53.37	-53.80	-58.44	-53.83	-53.27	-60.40
16.00	-2.32	-2.32	-51.85	-52.24	-56.25	-52.28	-51.96	-58.71
18.00	-2.56	-2.55	-51.54	-52.36	-53.28	-52.36	-52.66	-57.21
20.00	-2.66	-2.69	-53.22	-54.52	-52.82	-54.58	-55.23	-54.40
22.00	-2.80	-2.77	-53.61	-55.07	-49.14	-55.11	-57.20	-50.93
24.00	-3.12	-3.15	-51.84	-52.10	-48.87	-52.10	-59.92	-48.76
26.00	-3.14	-3.14	-49.59	-49.03	-47.22	-49.02	-62.06	-46.81
28.00	-3.29	-3.36	-46.33	-46.65	-46.57	-46.68	-55.31	-45.09
30.00	-3.40	-3.54	-47.84	-48.78	-46.84	-48.81	-51.15	-45.25
32.00	-3.41	-3.60	-48.17	-49.64	-49.45	-49.55	-49.80	-46.47
34.00	-3.71	-3.90	-47.89	-48.47	-50.84	-48.50	-48.65	-46.40
36.00	-3.72	-4.03	-48.26	-48.32	-47.29	-48.22	-48.40	-45.62
38.00	-4.31	-4.59	-47.26	-47.82	-44.34	-47.91	-47.82	-44.25
40.00	-4.16	-4.59	-47.89	-48.09	-45.85	-48.05	-47.53	-45.70
41.50	-4.60	-4.97	-50.87	-53.73	-51.67	-53.44	-49.08	-48.80
43.00	-4.58	-4.86	-50.78	-53.20	-55.61	-53.33	-50.74	-50.07
44.50	-4.67	-4.87	-49.52	-50.06	-54.89	-50.26	-51.42	-49.15
46.00	-4.56	-4.84	-46.71	-46.40	-50.64	-46.33	-51.69	-49.70
47.50	-5.52	-5.53	-48.24	-47.75	-51.30	-47.87	-50.48	-51.35
49.00	-5.18	-5.34	-46.74	-47.51	-52.49	-47.63	-49.19	-51.70
50.50	-4.99	-5.08	-46.48	-47.43	-51.24	-47.54	-47.50	-54.14
52.00	-5.36	-5.55	-47.83	-48.49	-51.34	-48.53	-46.13	-63.14
53.50	-5.58	-5.75	-46.97	-47.22	-52.28	-47.28	-44.60	-69.95
55.00	-6.03	-6.22	-44.02	-44.30	-51.01	-44.35	-42.37	-72.85
56.50	-5.57	-5.71	-45.18	-44.83	-48.05	-44.95	-41.76	-69.09
58.00	-5.86	-5.91	-44.47	-43.87	-46.77	-43.85	-42.99	-66.40
59.50	-5.76	-5.74	-43.14	-42.27	-44.90	-42.31	-44.48	-60.56
61.00	-6.48	-6.39	-44.75	-43.85	-43.77	-43.81	-46.20	-57.72
62.50	-7.00	-7.09	-46.29	-45.41	-43.51	-45.64	-48.65	-55.87
64.00	-7.44	-7.34	-42.54	-41.89	-44.09	-41.97	-47.39	-53.61
65.50	-8.14	-7.88	-44.77	-43.63	-45.40	-43.62	-45.07	-54.62
67.00	-7.83	-7.63	-46.23	-43.82	-46.00	-43.82	-44.96	-57.73

NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>



SP2T Solid-State Switch

RCS-1SP2T-A673

Typical Performance Data

Test Conditions: @ Temperature = +60°C, Pin = 8 dBm.

Freq. (GHz)	Return Loss, Active ports (dB)			RL, Terminated ports (dB)	
	COM	1	2	1	2
0.10	-21.07	-21.61	-21.60	-31.21	-31.18
0.50	-20.91	-20.85	-20.94	-33.29	-32.96
1.00	-21.64	-20.10	-20.45	-37.18	-34.98
2.50	-27.30	-18.88	-18.68	-37.93	-38.58
4.00	-22.13	-21.84	-20.84	-26.83	-26.52
6.00	-20.66	-25.68	-26.25	-28.46	-28.35
8.00	-22.87	-21.44	-20.51	-33.13	-33.40
10.00	-23.49	-22.94	-22.58	-25.49	-25.89
12.00	-22.06	-17.06	-16.77	-30.26	-33.31
14.00	-21.03	-19.75	-20.11	-25.81	-25.47
16.00	-16.90	-18.83	-18.86	-24.78	-30.11
18.00	-16.42	-16.49	-17.81	-28.90	-27.10
20.00	-18.30	-26.66	-22.35	-21.77	-22.75
22.00	-28.29	-19.25	-26.61	-18.94	-19.66
24.00	-17.33	-12.80	-12.61	-18.62	-20.35
26.00	-14.77	-18.89	-23.09	-17.20	-17.24
28.00	-18.59	-20.21	-20.40	-29.49	-27.22
30.00	-16.51	-19.44	-17.90	-18.12	-17.20
32.00	-18.31	-21.43	-19.51	-14.46	-13.79
34.00	-17.25	-13.67	-14.82	-27.74	-31.87
36.00	-19.83	-23.51	-22.69	-12.65	-12.90
38.00	-11.28	-12.10	-14.00	-13.50	-14.48
40.00	-15.45	-25.35	-29.84	-27.44	-31.64
41.50	-11.14	-10.76	-10.93	-10.28	-10.60
43.00	-23.95	-11.13	-11.96	-8.62	-9.20
44.50	-12.71	-10.96	-12.92	-15.50	-17.45
46.00	-18.35	-17.16	-18.51	-11.57	-12.79
47.50	-9.44	-8.35	-9.51	-8.19	-9.00
49.00	-12.10	-10.75	-11.14	-11.36	-11.64
50.50	-13.79	-14.75	-16.60	-19.22	-22.28
52.00	-12.46	-11.35	-11.08	-9.30	-9.71
53.50	-14.84	-11.46	-11.62	-9.02	-8.85
55.00	-9.25	-9.39	-9.18	-17.63	-16.70
56.50	-13.55	-23.91	-21.44	-12.90	-12.01
58.00	-11.67	-12.06	-12.13	-10.63	-10.99
59.50	-21.91	-13.23	-15.14	-13.89	-15.53
61.00	-13.18	-9.40	-10.77	-12.17	-14.42
62.50	-8.84	-9.09	-9.48	-7.16	-8.01
64.00	-8.55	-9.55	-11.50	-9.27	-10.20
65.50	-9.66	-6.41	-7.36	-9.66	-11.31
67.00	-23.33	-7.50	-8.13	-5.53	-5.90

NOTES:

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at <https://www.minicircuits.com/terms/viewterm.html>

