

Typical Performance Data

| FREQUENCY (GHz) | INSERTION LOSS (dB) | RETURN LOSS (dB) |
|--------------------|------------------------|---------------------|
| 22.0 | 65.34 | 0.24 |
| 22.2 | 83.41 | 0.19 |
| 22.4 | 71.94 | 0.10 |
| 22.7 | 80.04 | 0.10 |
| 22.9 | 81.02 | 0.02 |
| 23.2 | 77.59 | 0.01 |
| 23.4 | 82.51 | 0.07 |
| 23.6 | 83.21 | 0.13 |
| 23.9 | 88.77 | 0.18 |
| 24.1 | 82.95 | 0.16 |
| 24.4 | 84.48 | 0.11 |
| 24.6 | 87.54 | 0.06 |
| 24.8 | 86.64 | 0.04 |
| 25.1 | 84.53 | 0.01 |
| 25.3 | 80.18 | 0.00 |
| 25.6 | 91.87 | 0.02 |
| 25.8 | 77.38 | 0.02 |
| 26.0 | 83.96 | 0.04 |
| 26.3 | 78.58 | 0.03 |
| 26.5 | 65.02 | 0.02 |
| 26.8 | 53.21 | 0.02 |
| 27.0 | 34.19 | 0.08 |
| 27.1 | 21.01 | 0.24 |
| 27.2 | 3.79 | 3.90 |
| 27.4 | 0.95 | 12.01 |
| 27.5 | 0.58 | 17.24 |
| 27.6 | 0.49 | 17.88 |
| 27.7 | 0.51 | 15.58 |
| 27.8 | 0.50 | 15.37 |
| 28.0 | 0.38 | 27.15 |
| 28.1 | 0.48 | 15.67 |
| 28.2 | 0.41 | 27.17 |
| 28.3 | 0.65 | 15.92 |
| 28.8 | 34.96 | 0.02 |
| 29.3 | 54.71 | 0.07 |
| 29.8 | 66.54 | 0.07 |
| 30.2 | 74.90 | 0.05 |
| 30.7 | 71.96 | 0.01 |
| 31.2 | 86.73 | 0.07 |
| 31.7 | 78.04 | 0.21 |
| 32.2 | 86.29 | 0.15 |
| 32.6 | 80.05 | 0.09 |
| 33.1 | 75.07 | 0.13 |
| 33.6 | 77.97 | 0.04 |
| 34.1 | 90.38 | 0.03 |
| 34.6 | 79.24 | 0.05 |
| 35.5 | 74.75 | 0.07 |
| 36.5 | 64.74 | 0.09 |
| 37.4 | 53.34 | 0.10 |
| 38.4 | 31.63 | 0.03 |