

Typical Performance Data

FREQ.	Insertion Loss	Input Return Loss	Output Return Loss	FREQ.	Group Delay
(MHz)	(dB)	(dB)	(dB)	(MHz)	(ns)
25	101.62	28.33	28.28	17250	0.30
50	106.17	28.81	28.72	17275	0.30
100	104.09	30.86	30.17	17300	0.30
200	95.31	29.49	28.82	17325	0.30
300	91.87	28.52	27.84	17350	0.30
500	86.79	27.70	27.09	17375	0.30
700	84.29	27.11	26.46	17400	0.30
1000	81.09	26.75	26.36	17425	0.30
1200	79.80	26.67	26.50	17450	0.30
1400	78.54	26.70	26.61	17475	0.30
1600	77.56	27.23	27.28	17500	0.30
1800	76.65	27.28	27.86	17525	0.30
2000	76.00	28.01	28.82	17550	0.30
2500	72.67	30.24	33.42	17575	0.30
3000	67.73	32.42	44.66	17600	0.30
3500	62.85	30.06	30.90	17625	0.30
4000	58.93	26.08	24.79	17650	0.30
4500	55.89	22.30	20.80	17675	0.30
5000	53.59	19.88	18.30	17700	0.30
5500	52.18	17.86	16.25	17725	0.30
6000	51.56	16.41	14.91	17750	0.30
6500	52.06	15.12	13.76	17775	0.30
7000	53.70	14.46	13.10	17800	0.30
7500	57.17	14.15	12.77	17825	0.30
8000	61.86	13.80	12.41	17850	0.30
8500	60.29	14.08	12.72	17875	0.30
9000	60.02	14.83	13.46	17900	0.30
10975	30.04	19.30	19.05	17925	0.30
11400	20.41	19.21	17.26	17950	0.30
12275	10.06	17.58	16.80	17975	0.30
17500	5.08	11.20	16.22	18000	0.30
17600	5.09	11.31	16.01	18025	0.30
17700	5.09	11.43	15.75	18050	0.30
17800	5.10	11.59	15.50	18075	0.30
18000	5.12	11.99	15.26	18100	0.30
18100	5.17	12.33	15.38	18125	0.30
18200	5.17	12.71	15.50	18150	0.30
18300	5.17	13.24	15.76	18175	0.30
18400	5.19	13.77	16.14	18200	0.30
18500	5.18	14.59	16.62	18225	0.30
22075	10.07	22.05	8.95	18250	0.30
23650	20.09	21.67	7.53	18275	0.30
24475	30.25	18.05	7.15	18300	0.30
25000	38.73	15.08	7.01	18325	0.30
25500	48.23	12.94	7.28	18350	0.30
26000	57.77	11.55	7.93	18375	0.30
26400	60.50	10.97	8.79	18400	0.31
26600	61.12	10.73	9.38	18425	0.31
26800	61.31	10.61	10.03	18450	0.31
27000	59.66	10.51	10.76	18475	0.31
27500	58.20	10.69	12.45	18500	0.31
28000	57.83	11.17	13.40	18525	0.31
28500	57.30	11.96	12.89	18550	0.31
29000	56.76	13.16	11.53	18575	0.31
29500	55.66	14.93	10.14	18600	0.31
30000	54.92	17.46	9.08	18625	0.31
30500	53.97	20.47	8.38	18650	0.31
31000	53.63	22.01	7.92	18675	0.31
31500	51.95	19.70	7.83	18700	0.31
32000	50.35	16.58	8.26	18725	0.31