




Fixed Attenuators



FEATURES

- Wideband, 50Ω
- Input power up to 2W Max.
- 3, 6 and 10dB attenuation
- SMA Male and Female connectors
- Excellent VSWR, 1.20:1 to 1.40:1 typ.
- Excellent flatness, 0.30 to 0.45 typ.
- Length less than 1.5"



PRODUCT OVERVIEW

K3-VAT-A+ is a designer's kit consisting of three different attenuator models in the VAT-A+ family. There are two units per model for a total of six units. Mini-Circuits' VAT-A series are fixed attenuators operating from DC to 6000 MHz with excellent attenuation flatness. This attenuator series supports testing and measurement applications. Precise performance, excellent VSWR and rugged unibody construction makes this model an ideal solution for systems requiring precise attenuation.

K3-VAT-A+ ELECTRICAL SPECIFICATIONS

(3models, 2 of each, 6 total)

Model No. ¹	Frequency (GHz) f_L - f_U	Attenuation ² Flatness ³ (dB)					VSWR (:1)			Input Power ⁵ (W) Max.
		Nom. ⁴	DC-3 GHz	3-5 GHz	5-6 GHz	DC-6 GHz	DC-3 GHz	3-5 GHz	5-6 GHz	
			Typ.	Typ.	Typ.	Typ.	Typ.	Typ.	Typ.	
VAT-3A+	DC-6	3 ± 0.3	0.25	0.15	0.15	0.30	1.20	1.25	1.40	2.0
VAT-6A+	DC-6	6 ± 0.3	0.25	0.15	0.10	0.45	1.20	1.25	1.20	1.6
VAT-10A+	DC-6	10 ± 0.3	0.25	0.20	0.15	0.35	1.20	1.20	1.40	1.7

1. See individual model data sheets for more info.
2. Attenuation varies by 0.3 dB max over temperature.
3. Flatness = variation over band divided by 2.
4. Nominal attenuation at 10 MHz.
5. RF Power at 25°C. Check individual model data sheet for derated power at 85°C.