

Coaxial Switch

50Ω SP4T Pin Diode, Reflective TTL Driver 10 to 2500 MHz

ZSDR-425+



Generic photo used for illustration purposes only

CASE STYLE: GGG126

Connectors	Model
SMA	ZSDR-425+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power	L(+20 dBm), M(+28 dBm), U(+30 dBm)
Supply V	+6V max.
Permanent damage may occur if any of these limits are exceeded.	

Coaxial/Pin Connections

RF IN	RF-IN
RF OUT 1	RF-1
RF OUT 2	RF-2
RF OUT 3	RF-3
RF OUT 4	RF-4
TTL-1	TTL-1
TTL-2	TTL-2
+5V	+5V

Features

- wideband, 10 to 2500 MHz
- high isolation, 40 dB typ.

Applications

- test set-ups
- antenna switching
- satellite communication

Electrical Specifications (T_{AMB}=25°C)


MODEL NO.	FREQ. (MHz)		INSERTION LOSS (dB)				IN-OUT ISOLATION (dB)							
			Low band lw		Upper band U		L		M		U			
	f _L	f _U	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.
ZSDR-425(+)	10	2500	1.1	1.7	1.5	2.5	60	40	40	30	35	22		

L= low range (f_L to 10 f_L)

M=mid range (10 f_L to f_U/2)
lw=low band (f_L to f_U/2)

U=upper range (f_U/2 to f_U)

Outline Drawing



Outline Dimensions (Inch/mm)

A	B	C	D	E	F	G	H	J	K
2.25	1.38	1.24	.50	.150	3.100	.138	1.238	.30	.12
57.15	35.05	31.50	12.70	3.81	78.74	3.51	31.45	7.62	3.05
L	M	N	P	Q	R	S	T	wt	
.80	.69	--	.60	1.200	.52	.82	.150	grams	
20.32	17.53	--	15.24	30.48	13.21	20.83	3.81	80.0	


Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Control Logic






	TTL-1	TTL-2
RF-1	1	0
RF-2	1	1
RF-3	0	1
RF-4	0	0

REV. C
M151107
ZSDR-425+
WP/CP/AM
151007

Typical Performance Data

FREQ. (MHz)	ON (TTL LOW @ 0V) IN-OUT		INSERTION LOSS (dB) AMP. UNBAL.				OFF (TTL HIGH @ 5V) IN-OUT		ISOLATION (dB) DELTA		VSWR	
	\bar{x}	σ	\bar{x}	σ	\bar{x}	σ	\bar{x}	σ	\bar{x}	σ	IN	OUT (RF 1) ON OFF
											\bar{x}	\bar{x}
10.00	1.22	0.16	0.18	0.15	74.41	4.10	9.64	5.24	1.35	1.40	27.25	
20.00	1.06	0.12	0.15	0.12	70.64	2.69	8.25	4.56	1.19	1.22	27.08	
50.00	0.97	0.09	0.13	0.09	61.72	2.10	8.97	7.88	1.11	1.13	27.42	
100.00	0.94	0.09	0.12	0.09	56.09	1.46	6.48	2.94	1.10	1.11	26.82	
200.00	0.90	0.08	0.12	0.08	49.80	1.51	6.32	3.03	1.13	1.12	26.58	
408.40	1.01	0.07	0.11	0.07	45.66	1.36	5.61	1.32	1.21	1.18	26.03	
500.00	1.06	0.08	0.12	0.09	44.93	1.43	5.49	1.62	1.25	1.20	24.98	
669.85	1.10	0.07	0.12	0.07	44.06	1.59	5.94	1.86	1.30	1.24	24.36	
856.60	1.30	0.07	0.13	0.08	43.15	1.93	6.13	2.01	1.35	1.25	22.45	
1000.00	1.39	0.05	0.11	0.07	44.52	3.69	8.35	2.97	1.37	1.24	20.59	
1118.05	1.48	0.05	0.13	0.07	42.72	2.91	8.56	3.40	1.37	1.23	19.44	
1250.00	1.37	0.06	0.13	0.06	42.75	2.61	10.05	4.95	1.36	1.22	19.15	
1391.95	1.51	0.09	0.16	0.07	44.07	3.21	10.73	3.71	1.34	1.20	18.57	
1578.70	1.47	0.05	0.15	0.05	40.41	2.62	9.61	3.27	1.31	1.16	17.15	
1777.90	1.52	0.05	0.17	0.05	37.07	2.87	9.43	3.26	1.30	1.14	16.04	
2002.00	1.66	0.12	0.20	0.08	34.27	3.55	9.08	1.82	1.30	1.16	13.88	
2176.30	1.81	0.09	0.20	0.08	30.64	3.24	7.16	1.46	1.30	1.21	12.25	
2363.05	1.82	0.07	0.19	0.04	26.86	2.95	5.63	1.07	1.28	1.28	9.41	
2437.75	2.08	0.14	0.24	0.05	25.66	2.78	5.42	1.03	1.29	1.30	7.81	
2500.00	2.14	0.16	0.25	0.05	25.03	2.28	5.15	1.27	1.30	1.31	7.10	



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

