

Wideband


# Monolithic Amplifier Die

## TSY-172LNB-D+

50Ω 0.03 to 1.7 GHz

### The Big Deal

- Very wideband, 30 MHz – 1.7 GHz
- Low NF over entire frequency band, 1.4 dB
- Low current and low voltage (2.7V and 7.7 mA)
- Internal bypass switching



### Product Overview

TSY-172LNB-D+ (RoHS compliant) is an advanced Low Voltage, Low Current, Low Noise wideband Bypass amplifier Die fabricated using GaAs E-PHEMT technology offering extremely high dynamic range over a broad frequency range. It has integrated switches enabling users to bypass the amplifier.

### Key Features

| Feature   | Advantages  |
|---|---|
| Ultra-wideband: 30 MHz – 1.7 GHz                          | Ideal for a wide range of receiver applications including military, commercial wireless, and instrumentation. |
| Low Voltage & Low Current 2.7V & 7.7 mA                   | Ideal for Battery operated systems  |
| High IP3 24.7 dBm typ at 1 GHz                            | Provides enhanced linearity over broad frequency range under high signal conditions.                          |
| Internal bypass switch feature draws 0.2 mA during Bypass | Prolongs battery life by switching to bypass mode   |
| Unpackaged Die  | Enables the user to integrate the amplifier directly into hybrids   |



# Wideband Monolithic Amplifier Die

# TSY-172LNB-D+


50Ω 0.03 to 1.7 GHz

## Product Features

- Wideband: 0.03-1.7 GHz
- Built-in Bypass switching
- Low Noise figure: 1.4 dB typ.
- P1dB: +17.5 dBm typ.
- Low current and low voltage (2.7V and 7.7 mA)

## Typical Applications

- Wireless Base Station Systems
- Test and Measurement Systems
- Multi-Band Receivers



**+RoHS Compliant**


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

*Ordering Information: Refer to Last Page*

## General Description

TSY-172LNB-D+(RoHS compliant) is an advanced Low Voltage, Low Current, Low Noise wideband Bypass amplifier Die fabricated using GaAs E-PHEMT technology offering extremely high dynamic range over a broad frequency range. It has integrated switches enabling users to bypass the amplifier.


## Simplified Schematic and Pad description



| Pad# | Function       |
|------|----------------|
| 2    | RF-IN1         |
| 3    | RF-IN2         |
| 1    | Voltage Enable |
| 6    | RF-OUT1        |
| 5    | RF-OUT2 + DC   |
| 4    | Ground         |

Note: 1. Bond Pad material - Gold  
2. Bottom of Die - Gold plated

## Bonding Pad Position



Dimensions in  $\mu\text{m}$ , Typical

| L1 | L2 | L3    | L4  | L5  | H1  | H2  | H3    | H4  | H5  | H6  | H7  | Die Thickness | Bond Pad Size |
|----|----|-------|-----|-----|-----|-----|-------|-----|-----|-----|-----|---------------|---------------|
| 76 | 90 | 306.5 | 486 | 562 | 101 | 171 | 229.5 | 448 | 536 | 648 | 746 | 100           | 75 x 75       |

**Electrical Specifications<sup>1</sup> at 25°C, Zo=50Ω & V<sub>DD</sub>=2.7V unless otherwise noted**

| Parameter  | Condition (GHz) | Amplifier - ON |        |      | Amplifier - Bypass | Units |
|--|-----------------|----------------|--------|------|--------------------|-------|
|  |                 | Min.           | Typ.   | Max. | Typ.               |       |
| Frequency Range  |                 | 0.03           |        | 1.7  | 0.03 - 1.7         | GHz   |
| Noise Figure   | 0.03            |                | 1.3    |      | 0.3                | dB    |
|  | 0.5             |                | 1.2    |      | 0.8                |       |
|  | 1.0             |                | 1.4    |      | 1.3                |       |
|  | 1.5             |                | 1.8    |      | 1.8                |       |
|  | 1.7             |                | 1.9    |      | 2.4                |       |
| Gain/ Insertion loss                                     | 0.03            |                | 15.3   |      | -0.5               | dB    |
|  | 0.5             |                | 14.7   |      | -0.8               |       |
|  | 1.0             |                | 13.1   |      | -1.8               |       |
|  | 1.5             |                | 11.0   |      | -3.2               |       |
|  | 1.7             |                | 10.1   |      | -3.7               |       |
| Input Return Loss  | 0.03            |                | 13     |      | 19                 | dB    |
|  | 0.5             |                | 14     |      | 14                 |       |
|  | 1.0             |                | 10     |      | 8                  |       |
|  | 1.5             |                | 6      |      | 6                  |       |
|  | 1.7             |                | 6      |      | 5                  |       |
| Output Return Loss                                       | 0.03            |                | 16     |      | 18                 | dB    |
|  | 0.5             |                | 18     |      | 13                 |       |
|  | 1.0             |                | 14     |      | 7                  |       |
|  | 1.5             |                | 11     |      | 5                  |       |
|  | 1.7             |                | 10     |      | 6                  |       |
| Output Power at 1dB Compression, AMP-ON <sup>2</sup>     | 0.03            |                | 15.8   |      | 1.2                | dBm   |
|  | 0.5             |                | 17.1   |      | 2.7                |       |
|  | 1.0             |                | 17.5   |      | 3.1                |       |
|  | 1.5             |                | 17.8   |      | 2.6                |       |
|  | 1.7             |                | 17.4   |      | 1.4                |       |
| Output IP <sub>3</sub> <sup>3</sup>                      | 0.03            |                | 25.6   |      | 24.9               | dBm   |
|  | 0.5             |                | 26.4   |      | 28.4               |       |
|  | 1.0             |                | 24.7   |      | 30.4               |       |
|  | 1.5             |                | 24.0   |      | 23.5               |       |
|  | 1.7             |                | 22.4   |      | 19.5               |       |
| Device Operating Voltage (V <sub>DD</sub> )              |                 | 2.5            | 2.7    | 3.0  | 0                  | V     |
| Device Operating Current (I <sub>D+I<sub>e</sub></sub> ) |                 | —              | 7.7    | 10.6 | 0.2                | mA    |
| Enable Voltage (V <sub>e</sub> )                         |                 | 2.5            | 2.7    | 3.0  | 0                  | V     |
| Device Current Variation vs. Temperature <sup>4</sup>    |                 |                | 1.5    |      | —                  | μA/°C |
| Device Current Variation vs. Voltage                     |                 |                | 0.0067 |      | —                  | mA/mV |
| Thermal Resistance, junction-to-ground lead              |                 |                | 229    |      | —                  | °C/W  |

1. Measured on Mini-Circuits Characterization Test Board Die packaged in 2x2 mm, 8-lead MCLP package and soldered on TB-943+. See Characterization Test Circuit (Fig. 1)

2. Current increases to 28-54 mA typ. at P1dB

3. Tested at Pout=+6 dBm/tone

4. ((Current at 85°C - Current at -45°C)/130)

**Absolute Maximum Ratings<sup>5</sup>**

| Parameter                           | Ratings  |
|-------------------------------------|--|
| Operating Temperature (ground lead) | -40°C to 85°C  |
| Total Power Dissipation             | 0.2W   |
| Input Power                         | Amplifier - ON 10 dBm (continuous), +23 dBm (5 min. max)   |
|                                     | Amplifier Bypass 15 dBm (continuous), +22 dBm (5 min. max) |
| DC Voltage V <sub>DD</sub>          | 6V   |
| DC Voltage Enable                   | 6V   |

5. Permanent damage may occur if any of these limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.

|  | Min. | Typ. | Max. | Units |
|--|------|------|------|-------|
| Amplifier-ON (V <sub>DD</sub> , V <sub>e</sub> )     | 2.5  | 2.7  | 2.9  | V     |
| Amplifier-Bypass (V <sub>DD</sub> , V <sub>e</sub> ) | —    | —    | 0.3  |       |

Switching Specifications

| Parameter               |                               | Min. | Typ. | Max. | Units |
|-------------------------|-------------------------------|------|------|------|-------|
| Amplifier ON to Bypass  | OFF TIME (50% Control to 10%) | —    | 6    | —    | μS    |
|                         | FALL TIME (90 TO 10% RF)      | —    | 7    | —    |       |
| Amplifier Bypass to ON  | ON TIME (50% Control to 90%)  | —    | 59   | —    | μS    |
|                         | RISE TIME (10% to 90% RF)     | —    | 20   | —    |       |
| Control Voltage Leakage |                               | —    | 443  | —    | mV    |

Characterization Test Circuit (For reference)





Fig 1. Block Diagram of Test Circuit used for characterization. (Die packaged in 2x2 mm, 8-Lead package soldered on Mini-Circuits Characterization test board TB-943+)

Gain, Return loss, Output power at 1dB compression (P1dB), output IP3 (OIP3) and noise figure measured using Agilent’s N5242A PNA-X microwave network analyzer.

Conditions:

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, +6 dBm/tone at output.
3. Switching Time RF Signal: Pin=-10 dBm at 500 MHz. VDD=Venable=0 to 2.5 / 2.7 / 2.9V, Pulse Signal=500 Hz, 50% duty cycle.

## Assembly Diagram



## Assembly and Handling Procedure

- Storage**  
 Dice should be stored in a dry nitrogen purged desiccators or equivalent.
- ESD**  
 MMIC GaAs E-PHEMT amplifier dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
- Die Attach**  
 The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030HK-PT/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic die pick up tools only.
- Wire Bonding**  
 Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the die to the package or substrate. All bond wires should be kept as short as low as reasonable to minimize performance degradation due to undesirable series inductance.

| <b>Additional Detailed Technical Information</b><br><i>additional information is available on our dash board.</i> |   |
|---|---|
| <b>Performance Data</b>   | Data Table  |
|   | Swept Graphs  |
|   | S-Parameter (S2P Files) Data Set (.zip file)  |
| <b>Case Style</b>   | Die   |
| <b>Die Ordering and packaging information</b>   | Quantity, Package <span style="float: right;">Model No.</span>  |
|   | Small, Gel - Pak: 5,10,50,100 KGD* <span style="float: right;">TSY-172LNB-DG+</span><br>Medium†, Partial wafer: KGD*<2385 <span style="float: right;">TSY-172LNB-DP+</span><br>Large†, Full Wafer <span style="float: right;">TSY-172LNB-DF+</span> |
|   | †Available upon request contact sales representative  |
|   | Refer to <a href="#">AN-60-067</a>  |
| <b>Environmental Ratings</b>  | ENV80   |

\*Known Good Dice ("KGD") means that the dice in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such dice fall within a predefined range. While DC testing is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

**ESD Rating\*\***

Human Body Model (HBM): Class 1A (Pass 250V) in accordance with ANSI/ESD STM 5.1 - 2001

\*\* Tested in industry standard MCLP 2X2 mm, 8-lead package.

**Additional Notes**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.