

Bandpass Filter

50Ω 520 to 640 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input*	0.5W at 25°C

*Passband rating, derate linearly to 0.25W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

Pin Connections

RF IN	1
RF OUT	8
GROUND	2,-7,9-14

Outline Drawing



Suggested Layout
Tolerance to be within ±.002

METALLIZATION SOLDER RESIST


Outline Dimensions (inches)

A	B	C	D	E	F	G	H
.365	1.360	.35	.100	.180	.140	.100	.100
9.27	34.54	8.89	2.54	4.57	3.56	2.54	2.54


J	K	L	M	N	P	Q	Wt.
.305	.150	.120	.275	.152	.405	1.400	grams
7.75	3.81	3.05	6.99	3.86	10.29	35.56	4.0

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-363+ Suggested PCB Layout (PL-227)



NOTES: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025 ± .002" COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- Linear phase, up to ±6 deg typ @ Fc ± 60 MHz
- High rejection
- Shielded case
- Aqueous washable

Applications

- Military radio
- Harmonic rejection
- Transmitters/receivers



Generic photo used for illustration purposes only

CASE STYLE: HQ1157


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 4dB)	STOPBANDS (MHz)				MAXIMUM DEVIATION FROM LINEAR PHASE (deg.)	VSWR (:1)		
		Loss > 20dB		Loss > 40dB			Passband		Stopband
		F3	F4	F5	F6		Typ.	Max.	Typ.
Fc	F1 - F2					Fc ± 60MHz			
580	520 - 640	440	720	380	760-2500	±11	1.4	1.9	20

Typical Frequency Response





Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Deviation from Linear Phase (deg.)
0.5	95.26	1980.07	520	3.84
100	76.30	2647.93	525	1.52
380	56.02	53.15	530	-0.14
440	29.37	19.85	540	-1.98
465	16.02	7.35	550	-2.34
480	7.55	4.68	560	-1.72
495	4.19	2.23	570	-0.83
520	2.52	1.63	575	-0.48
550	2.06	1.39	580	0.26
580	1.94	1.32	585	1.02
600	1.99	1.27	590	1.75
640	2.40	1.18	595	2.42
670	5.93	2.39	600	2.96
690	14.73	6.25	610	3.45
720	34.40	17.09	620	2.68
760	54.52	17.82	630	0.01
1000	71.03	23.12	635	-2.33
2500	59.76	27.65	640	-5.52



Surface Mount Band Pass Filter

BPF-A580+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C	@ -40° C	@ +25° C	@ +85° C
0.5	89.50	90.09	94.48	0.00	0.00	0.00	0.00	0.01	0.01
100	75.99	75.63	76.45	0.01	0.03	0.05	0.49	0.57	0.61
200	93.97	91.76	97.99	0.06	0.10	0.13	0.53	0.68	0.80
300	77.27	77.18	76.50	0.18	0.22	0.25	0.76	0.93	1.05
380	57.72	57.59	57.48	0.37	0.43	0.48	1.22	1.51	1.76
400	48.86	48.72	48.61	0.46	0.54	0.58	1.05	1.30	1.50
440	27.94	27.78	27.59	0.82	0.95	1.05	1.23	1.50	1.70
450	22.29	22.09	21.85	1.02	1.18	1.31	1.59	1.93	2.19
460	16.50	16.28	16.01	1.39	1.62	1.82	2.23	2.73	3.16
465	13.63	13.42	13.16	1.72	2.00	2.26	2.76	3.39	3.97
470	10.87	10.71	10.50	2.23	2.59	2.94	3.51	4.29	5.07
480	6.32	6.40	6.41	4.21	4.73	5.26	5.84	6.81	7.77
490	3.84	4.12	4.33	7.31	7.81	8.38	8.53	9.09	9.49
495	3.23	3.55	3.79	8.78	9.28	9.88	9.58	9.96	10.20
500	2.85	3.17	3.42	10.04	10.60	11.31	10.51	10.87	11.09
510	2.41	2.72	2.96	12.16	12.93	14.01	12.39	12.98	13.51
520	2.16	2.46	2.70	14.01	14.84	16.06	14.16	15.04	16.08
530	2.00	2.31	2.56	15.26	15.85	16.65	15.29	16.18	17.38
540	1.91	2.23	2.49	15.52	15.73	15.87	15.56	16.14	16.81
550	1.85	2.18	2.45	15.28	15.24	14.95	15.36	15.61	15.66
560	1.80	2.13	2.42	15.37	15.24	14.73	15.37	15.42	15.10
570	1.74	2.07	2.36	16.40	16.30	15.67	16.19	16.19	15.69
580	1.69	2.02	2.31	19.02	19.04	18.30	18.59	18.71	18.15
590	1.66	2.00	2.29	23.53	23.38	22.25	24.60	25.39	24.90
600	1.69	2.05	2.36	22.76	21.74	20.56	33.91	33.09	32.67
620	1.88	2.27	2.61	17.64	17.55	17.00	18.39	18.38	17.98
630	1.98	2.40	2.76	20.46	21.54	22.19	17.67	17.88	17.81
640	2.27	2.76	3.19	17.26	17.00	17.12	14.28	14.07	13.97
650	3.08	3.69	4.24	9.49	9.22	9.00	8.95	8.81	8.66
660	4.39	5.06	5.68	5.67	5.66	5.58	5.72	5.82	5.80
670	5.42	6.00	6.58	4.33	4.55	4.64	4.58	4.93	5.09
680	5.16	5.78	6.48	5.69	6.38	6.68	6.70	7.96	8.75
690	7.55	9.64	11.48	4.98	4.13	3.63	7.27	5.91	5.17
700	17.04	18.98	20.66	1.53	1.65	1.71	2.06	2.24	2.33
720	32.56	33.99	35.24	0.92	1.09	1.19	1.12	1.35	1.49
750	49.84	50.96	51.81	0.87	1.03	1.15	0.89	1.10	1.23
760	54.87	55.80	56.90	0.89	1.06	1.18	0.87	1.07	1.19
800	73.13	71.72	74.01	1.04	1.25	1.44	0.83	1.03	1.17
900	77.73	77.41	78.22	1.08	1.37	1.61	1.02	1.31	1.58
1000	72.12	72.37	72.74	0.68	0.88	1.03	1.56	2.04	2.45
1100	74.95	75.29	76.58	0.53	0.67	0.78	2.21	2.62	2.91
1200	70.17	85.61	64.90	0.48	0.61	0.71	1.95	2.30	2.62
1300	70.10	70.89	68.65	0.46	0.63	0.75	5.02	7.21	9.42
1400	60.20	57.51	60.80	0.49	0.71	0.89	1.37	1.68	1.94
1500	62.77	65.46	64.99	0.53	0.82	1.06	0.87	1.21	1.48
1600	66.25	71.15	70.90	0.57	0.91	1.20	0.71	1.06	1.33
1700	74.98	74.31	77.03	0.60	0.94	1.25	0.62	0.97	1.25
1800	82.67	80.37	87.00	0.60	0.93	1.25	0.54	0.90	1.18
1900	75.97	74.50	75.93	0.58	0.89	1.20	0.49	0.83	1.12
2000	86.61	88.31	84.08	0.55	0.85	1.13	0.44	0.78	1.06
2100	95.23	91.76	81.49	0.52	0.81	1.08	0.40	0.72	1.01
2200	74.84	77.32	77.74	0.49	0.76	1.01	0.35	0.68	0.96
2300	79.70	66.68	73.41	0.46	0.73	0.96	0.33	0.64	0.91
2400	67.76	65.66	68.44	0.44	0.70	0.92	0.30	0.60	0.86
2500	63.81	61.87	61.77	0.42	0.68	0.89	0.26	0.57	0.81

REV. X1

BPF-A580+

091124

Page 1 of 2



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



Surface Mount Band Pass Filter

BPF-A580+

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@ -40° C	@ +25° C	@ +85° C
520	9.58	9.55	9.51
521	9.52	9.48	9.45
522	9.46	9.41	9.38
523	9.39	9.35	9.32
524	9.34	9.28	9.27
525	9.27	9.23	9.20
526	9.22	9.18	9.16
527	9.17	9.12	9.10
528	9.10	9.07	9.03
529	9.05	9.01	8.99
530	8.99	8.96	8.94
531	8.94	8.91	8.88
532	8.90	8.86	8.84
533	8.85	8.81	8.78
534	8.80	8.76	8.73
535	8.75	8.72	8.68
536	8.72	8.68	8.65
537	8.67	8.64	8.61
538	8.63	8.59	8.57
539	8.59	8.56	8.53
540	8.56	8.53	8.50
541	8.52	8.49	8.46
542	8.50	8.46	8.44
543	8.45	8.42	8.39
544	8.42	8.40	8.36
545	8.39	8.36	8.32
546	8.36	8.33	8.29
547	8.33	8.30	8.25
548	8.31	8.28	8.25
549	8.27	8.24	8.20
550	8.25	8.22	8.18
551	8.22	8.19	8.16
552	8.20	8.18	8.14
553	8.17	8.15	8.11
554	8.14	8.13	8.09
555	8.11	8.10	8.05
560	8.09	8.08	8.05
565	8.07	8.07	8.04
570	8.07	8.07	8.05
575	8.07	8.07	8.07
580	8.09	8.10	8.11
585	8.13	8.15	8.16
590	8.18	8.20	8.22
595	8.24	8.27	8.30
600	8.32	8.35	8.38
605	8.41	8.45	8.48
610	8.53	8.58	8.62
615	8.69	8.75	8.80
620	8.91	8.98	9.05
625	9.17	9.26	9.34
630	9.48	9.57	9.66
635	9.79	9.87	9.96
640	10.07	10.14	10.22

REV. X1
BPF-A580+
091124
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE




INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE




Typical Performance Curves



Outline Dimensions

HQ1157



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
HQ1157	.365 (9.27)	1.360 (34.54)	.350 (8.89)	.100 (2.54)	.180 (4.57)	.140 (3.56)	.100 (2.54)	.100 (2.54)	.305 (7.75)	.150 (3.81)	.120 (3.05)	.275 (6.99)

CASE#	N	P	Q	WT.GRAM
HQ1157	.152 (3.87)	.405 (10.29)	1.400 (35.56)	4.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RFIIF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F83

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
56	16	13	100

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M101212	NEW RELEASE (FROM RAVON)	11/05	DK	YB
A	M108938	SWITCH HATCHES	12/06	DK	HH
B	M118075	CHANGE LINE PLACES	06/08	HB	HH
C	M173459	CORRECTED CASE STYLE & TB PART#	03/27/19	ITG	IL

SUGGESTED MOUNTING CONFIGURATION
FOR HQ1157 CASE STYLE, rf PIN CONNECTION




NOTE:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS $.025" \pm .002"$. COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005 ANGLES $\pm$ FRACTIONS $\pm$	DRAWN	HB (RAVON)	12 JUN 2008
	CHECKED	RZ (RAVON)	12 JUN 2008
	APPROVED	HH (RAVON)	12 JUN 2008



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235


PL, rf, HQ1157, TB-363+, 50 OHM

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-227	C
FILE:	98PL227	SCALE:	2:1
		SHEET:	1 OF 1

Evaluation Board and Circuit



TB-363+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS R04350 or equivalent, Dielectric Constant=3.48, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D