


Outline Dimensions

H557-1



CASE#	A	B	C	D	E	F	G	H	J	K	L
H557-1	1.25 (31.75)	1.25 (31.75)	.75 (19.05)	.63 (15.88)	.38 (9.53)	1.000 (25.40)	.125 (3.18)	.125 (3.18)	.718 (18.24)	.27 (6.76)	.255 (6.48)

CASE#	M	N	P	Q	R	S	T	WT.GRAMS
H557-1	.240 (6.10)	1.69 (42.88)	.75 (19.05)	.13 (3.18)	2.20 (55.83)	.75 (19.05)	.06 (1.52)	37

Dimensions are in inches (mm). Tolerances: 2PL. ± .03; 3PL. ± .015

Notes:

1. Case material: Aluminum alloy.
2. Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
3. Refer to the individual model data sheet for the type of connectors available.
4. Mounting bracket available on request. Add suffix B to part number.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS