

TCM3-1TX+

 50Ω 2 to 500 MHz

The Big Deal

- Low amplitude unbalance, 0.3 dB typ.
- Excellent phase unbalance, 2 deg. typ.
- Small size, 0.16 x 0.15 x 0.16"





CASE STYLE: DB1627

Product Overview

TCM3-1TX+ is a 50Ω surface-mount, DC-isolated transformer with a secondary center tap, covering the 2 to 500 MHz band. This model provides a 3:1 secondary/primary impedance ratio and is capable of handling up to 0.25W RF input power. It provides 0.3 dB typ. amplitude unbalance and 2° phase unbalance. Featuring core and wire construction mounted on a 6-lead plastic base with tin over nickel termination finish, the unit measures 0.16 x 0.15 x 0.16" to accommodate dense circuit board layouts. It also incorporates Mini-Circuits' Top Hat® feature for faster, more accurate pick-and-place assembly.

Key Features

Feature	Advantages
Low unbalance: - 0.3 dB typ. amplitude unbalance - 2° phase unbalance	Low unbalance improves a system's electromagnetic compatibility by rejecting unwanted commonmode noise.
DC isolation	Provides DC isolation between circuits and efficient AC transmission, eliminating the need for external DC biasing components.
Secondary center tap	Allows DC feed up to 30 mA and DC bias without adding bias tees into the signal chain.
Small footprint (0.16 x 0.15 x 0.16")	Accommodates tight space requirements for dense PCB layouts.
Top Hat [®] feature	Improves speed and accuracy of pick and place assembly and provides clear device marking for visual inspection.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.ninicircuits.com/MCLStore/terms.jsp

TCM3-1TX+

2 to 500 MHz

-20°C to 85°C

-55°C to 100°C

0.25W

30mA



Features

- Excellent amplitude unbalance. 0.3 dB typ.
- Excellent phase unbalance, 2 deg. typ. in 1 dB bandwidth
- Plastic base with solder plated leads
- · Aqueous washable

Applications

Impedance matching

CASE STYLE: DB1627 +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Pin Connections

Maximum Ratings

Operating Temperature

Storage Temperature

 50Ω


RF Power

DC Current

PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	1
SECONDARY	3
SECONDARY CT	2
NOT USED	5

Permanent damage may occur if any of these limits are exceeded.

Outline Drawing





Suggested Layout, Tolerance to be within .002

Parameter	Frequency (MHz)	Min.	Тур.	Max.	Unit
Impedance Ratio (Secondary/Primary)	-	-	3	-	Ω
Frequency Range	-	2	-	500	MHz
Insertion Loss	2-500	-	0.4	2	٩D
insertion Loss	5-300	-	0.3	1	dB

Electrical Specifications at 25°C


Typical Performance Data


FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
1	0.68	15.11	
2	0.44	18.06	
2 3	0.34	19.73	
5	0.24	21.64	
10	0.17	23.62	
100	0.25	24.61	
125	0.27	24.27	
150	0.28	24.36	
175	0.29	24.00	
200	0.31	23.71	
225	0.32	23.34	
250	0.33	22.89	
275	0.34	22.50	
300	0.36	22.23	
325	0.37	21.81	
350	0.38	21.40	
375	0.40	21.05	
400	0.41	20.74	
450	0.45	19.97	
500	0.48	19.35	


Outline Dimensions (inch)

F	E	D	С	В	Α
.025	.040	.050	.160	.150	.160
0.64	1.02	1.27	4.06	3.81	4.06
wt		K	J	Н	G
grams		.030	.190	.065	.028
0.15		0.76	4.83	1.65	0.71

Config. A







- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Insertion Loss is referenced to mid-band loss, 0.5 dB typ.

RF Transformer TCM3-1TX+


Typical Performance Data

FREQ.	INSERTION LOSS	RETURN LOSS
(MHz)	(dB)	(dB)
1	0.68	15.11
2	0.44	18.06
3	0.34	19.73
5	0.24	21.64
10	0.17	23.62
25	0.17	24.71
50	0.21	24.84
75	0.23	24.85
100	0.25	24.61
125	0.27	24.27
150	0.28	24.36
175	0.29	24.00
200	0.31	23.71
225	0.32	23.34
250	0.33	22.89
275	0.34	22.50
300	0.36	22.23
325	0.37	21.81
350	0.38	21.40
375	0.40	21.05
400	0.41	20.74
425	0.43	20.39
450	0.45	19.97
475	0.47	19.61
500	0.48	19.35

RF Transformer TCM3-1TX+

Typical Performance Curves








Case Style



DB1627

Outline Dimensions



CASE#	A	В	C	D	Е	F	G	Н	J	K	WT. GRAM
DB1627	.160	.150	.160	.050	.040	.025	.028	.065	.190	.030	15
DB1027	(4.06)	(3.81)	(4.06)	(1.27)	(1.02)	(0.64)	(0.71)	(1.65)	(4.83)	(0.76)	.13

Dimensions are in inches (mm). Tolerances: 2 Pl. \pm .01; 3Pl. \pm .005

Notes:

- 1. Case material: Plastic.
- 2. Termination finish:

For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

- 3 Orientation dot on top hat & orientation feature on substrate correspondence to pin #1.
- 4 Top-Hat total thickness: .013 inches MAX.






P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F47

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
12	8	13	1000, 2000
		7	20, 50, 100, 200, 500

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET http://www.minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION	
Ψ	

		REVISIONS			
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M106563	NEW RELEASE	08/23/06	AV	IG

SUGGESTED MOUNTING CONFIGURATION FOR AT224/DB714 CASE STYLE, "gs/ha/hd" PIN CONNECTIONS (FOR SINGLE ENDED TO BALANCED APPLICATION)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. ON EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
 - 3. THIS PAD IS NOT REQUIRED FOR AT224 CASE STYLE.


DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK


UNLESS OTHERWISE SPECIFIED		INITIALS	DATE		¬		•	• 4 ®		
DIMENSIONS ARE IN INCHES	DRAWN	AV	07/28/06		⊔ Mını	$\mathbf{U} - \mathbf{C}$	ircu	$ m lts$ 13	Neptu	ne Avenue NY 11235
TOLERANCES ON:	CHECKED	IL	08/23/06					БГС	OKIJII	NI III
3 PL DECIMALS ± .005	APPROVED	IG	08/23/06							
FRACTIONS ±				PL.	gs/ha/hd	. AT22	24/DB714	4. TC/T(CM.	TB-145
□ Mini	-Circuits ®		•]	6-77	,	-,	-,, -	,	
THIS DOCUMENT AND ITS CONTENTS EXCEPT FOR USE EXPRESSLY GRANTE				CIZE	CODE IDENT	DDAWING	NO			DEV
AND THE UNITED STATES GOVERNMEN	IT, MINI-CIRCUITS	RESERVES ALL P		SIZE		DRAWING	98-PL	244		OR
DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY. IN WHOLE OR IN PART. WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.			A	15542		90-PL	-244 		UK	
PARIT, IN WHOLE OR IN PARI, WITH	OUT WRITTEN PERMISSION OF MINI-CIRCUITS.		FILE: C	8PL244	SCALE:	8:1	SHEET:	1	OF 1	
	ASHEETA1.	WG REV:A DA	TE:01/12/95	5	07 L≈44		0.1		T	Or I

Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT



TB-145



Schematic Diagram

Notes:

- 1. 50 Ohm SMA Female connectors.
- 2. PCB Material: Rogers RO4350B or its equivalent, III Mini-Circuits® Dielectric Constant=3.5, Thickness=.020"



Environmental Specifications

ENV02

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-20° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

ENV02 Rev: A

02/25/11

M130240 File: ENV02.pdf

This document and its contents are the property of Mini-Circuits.