

DC Pass

Matching Transformer

Z7550-NMNF+

50/75Ω

DC to 2300 MHz

The Big Deal

- Low matching loss of 0.5 dB typical
- Wideband coverage, DC-2300MHz
- Maximum DC current handling capability of 5A
- Connectorized package



Generic photo used for illustration purposes only
CASE STYLE: H795-4

Product Overview

Z7550-NMNF+ is a DC passing matching transformer that allows impedance matching between 50Ω and 75Ω systems with minimum reflection in to the circuit. This matching transformer will find its application in any system where 50Ω-75Ω matching is required

Key Features

Feature	Advantages
Low insertion loss	This introduced minimum reflection in to the circuit.
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Matching Transformer

50/75Ω

DC to 2300 MHz

Z7550-NMNF+



Generic photo used for illustration purposes only

CASE STYLE: H795-4

Connectors Model

75Ω N-F Z7550-NMNF+

50Ω N-M

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
DC Current	5A max.
DC Resistance	0.2Ω max.

Permanent damage may occur if any of these limits are exceeded.

Features

- Low matching loss of 0.5 dB typical
- Wideband coverage, DC-2300MHz
- Maximum DC current handling capability of 5A
- Connectorized package


Applications

- Impedance matching

Coaxial Connections

Input	N-Male
Output	N-Female

Outline Drawing




Outline Dimensions (inch mm)

A	B	C	D	E
1.25	1.25	0.94	0.63	0.47
31.75	31.75	23.88	16.00	11.94
F	G	H	wt	
1.00	0.13	0.13	grams	
25.40	3.18	3.18	91	

Note: Please refer to case style drawing for details

Functional Schematic





Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range	-	DC	-	2300	MHz
Insertion Loss	10	-	-	1.0	dB
	950-2300	-	0.5	1.2	
VSWR	10	-	-	1.8	:1
	950-2300	-	-	1.5	
Power	DC-2300	-	-	2.0	W

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	VSWR	
		50 Ω	75 Ω
10	0.01	1.50	1.50
20	0.02	1.50	1.50
100	0.08	1.51	1.48
250	0.23	1.50	1.47
300	0.28	1.49	1.46
950	0.16	1.11	1.12
1000	0.17	1.08	1.09
1500	0.23	1.07	1.06
2000	0.35	1.27	1.28
2300	0.40	1.19	1.22

Z7550-NMNF+
INSERTION LOSSZ7550-NMNF+
VSWR

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com



Typical Performance Data

FREQ.	INSERTION LOSS	INPUT RETURN LOSS (50Ω)	OUTPUT RETURN LOSS (75Ω)
(MHz)	(dB)	(dB)	(dB)
1.00	0.01	13.99	13.98
5.00	0.01	13.97	13.99
10.00	0.01	13.96	14.01
20.00	0.02	13.94	14.04
50.00	0.04	13.89	14.12
100.00	0.08	13.86	14.23
150.00	0.13	13.87	14.31
200.00	0.18	13.91	14.39
250.00	0.23	13.98	14.46
300.00	0.28	14.11	14.55
350.00	0.33	14.30	14.67
400.00	0.36	14.53	14.83
450.00	0.37	14.85	15.07
500.00	0.37	15.28	15.38
550.00	0.35	15.80	15.79
560.00	0.34	15.91	15.88
570.00	0.33	16.02	15.97
580.00	0.33	16.14	16.08
590.00	0.32	16.27	16.19
600.00	0.31	16.40	16.30
650.00	0.26	17.14	16.92
700.00	0.22	18.06	17.69
750.00	0.19	19.15	18.63
800.00	0.17	20.43	19.78
850.00	0.16	22.01	21.16
900.00	0.16	23.88	22.86
950.00	0.16	25.95	24.91
1000.00	0.17	28.48	27.42
1050.00	0.17	31.53	30.50
1100.00	0.18	33.85	34.00
1150.00	0.18	34.37	36.42
1200.00	0.19	33.61	35.94
1250.00	0.20	32.39	34.33
1300.00	0.20	31.58	33.12
1350.00	0.21	31.29	32.46
1400.00	0.21	31.01	32.21
1450.00	0.22	30.38	31.87
1500.00	0.23	29.40	31.06
1550.00	0.24	28.04	29.51
1600.00	0.25	26.41	27.44
1650.00	0.25	24.74	25.47
1700.00	0.25	23.23	23.69
1750.00	0.25	21.95	22.15
1800.00	0.26	20.85	20.90
1850.00	0.26	19.94	19.89
1900.00	0.28	19.30	19.08
1950.00	0.31	18.84	18.50
2000.00	0.35	18.56	18.13
2050.00	0.39	18.50	17.95
2075.00	0.40	18.55	17.93
2100.00	0.42	18.65	17.96
2135.00	0.43	18.86	18.09
2140.00	0.43	18.90	18.11
2145.00	0.43	18.94	18.14
2150.00	0.43	18.98	18.17
2155.00	0.43	19.02	18.20
2160.00	0.43	19.08	18.23
2200.00	0.43	19.54	18.58
2250.00	0.42	20.28	19.21
2300.00	0.40	21.18	20.05

DC Pass Matching Transformer


Z7550-NMNF+

Typical Performance Curves



Outline Dimensions

H795-4



CASE#	A	B	C	D	E	F	G	H	WT.GRAMS
H795-4	1.25 (31.75)	1.25 (31.75)	.94 (23.88)	.63 (16.00)	.47 (11.94)	1.000 (25.40)	.125 (3.18)	.125 (3.18)	91

Dimensions are in inches (mm). Tolerances: 2PL. $\pm .03$; 3PL. $\pm .015$

Notes:

1. Case material: Aluminum alloy.
2. Case finish:

For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I