

Ceramic Bandpass Filter

BFCN-1900+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	VSWR (:1)	GROUP DELAY (ns)
100	66.39	138.63	0.00
300	57.20	111.73	0.00
500	53.03	102.96	0.02
700	50.51	97.53	0.03
900	48.95	97.96	0.02
1000	48.53	94.67	0.04
1100	48.36	95.69	0.03
1200	48.68	92.97	0.04
1300	49.71	91.46	0.03
1427	53.74	84.51	0.00
1660	50.31	45.30	0.94
1750	20.63	14.74	0.84
1800	6.13	2.56	4.60
1850	3.94	2.45	4.57
1873	3.10	1.67	3.55
1883	2.85	1.41	3.57
1893	2.68	1.23	3.54
1903	2.59	1.18	3.47
1913	2.56	1.21	3.41
1920	2.56	1.23	3.37
1930	2.60	1.24	3.38
1940	2.67	1.22	3.45
1950	2.83	1.25	3.58
1960	3.13	1.43	3.71
2000	6.53	4.20	3.58
2063	14.89	17.27	1.93
2126	21.72	35.57	0.78
2153	24.20	43.19	0.47
4500	33.62	95.34	0.03
5500	32.30	90.59	0.03
7000	24.46	151.95	0.18
8000	31.13	115.87	0.07
9000	25.40	45.51	0.06
10000	18.13	24.80	0.10

