



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
UP2912	.800 (20.32)	2.100 (53.34)	.580 (14.73)	.095 (2.41)	1.910 (48.51)	.160 (4.06)	.210 (5.33)	.075 (1.91)	.115 (2.92)	.155 (3.94)	1.680 (42.67)	1.755 (44.58)	1.870 (47.50)

CASE#	P	Q	R	S	T	U	V	WT.GRAM
UP2912	1.950 (49.53)	2.140 (54.36)	.840 (21.34)	.650 (16.51)	.570 (14.48)	.555 (14.10)	1.783 (45.29)	40

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

### Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 2-5µinch (.05-.13microns) Gold over 120-240µinch (3.05-6.10microns) Nickel plate.  
All models, (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS