

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10	76.14	0.05
50	60.58	0.05
100	54.55	0.05
200	48.68	0.05
300	45.57	0.05
400	43.68	0.06
500	42.58	0.06
600	42.02	0.07
700	42.23	0.07
800	43.25	0.07
900	45.61	0.08
1000	51.94	0.09
1100	57.33	0.10
1200	43.78	0.11
1350	35.13	0.12
1400	32.99	0.13
1500	29.33	0.15
1600	25.96	0.17
1700	22.77	0.21
1800	19.53	0.28
1900	16.19	0.41
2000	12.54	0.69
2100	8.46	1.46
2200	4.30	4.07
2300	1.68	14.79
2400	1.40	15.05
2410	1.42	14.26
2420	1.44	13.68
2430	1.47	13.26
2440	1.48	12.98
2450	1.50	12.83
2460	1.52	12.79
2470	1.53	12.87
2480	1.54	13.06
2490	1.55	13.36
2500	1.56	13.76
2600	2.31	10.72
2700	5.89	3.05
2800	11.10	1.06
2900	16.05	0.50
3000	20.55	0.30
3200	28.87	0.18
3400	37.65	0.16
3600	47.88	0.17
3800	47.36	0.18
4000	42.69	0.21
4200	40.96	0.24
4400	40.51	0.28
4600	40.66	0.32
4800	41.17	0.35
5000	42.04	0.39
5200	43.06	0.41
5400	44.41	0.42
5600	46.42	0.42
5800	49.29	0.41
6000	52.98	0.39
6200	53.60	0.35
6400	52.74	0.32
6600	51.16	0.28
6800	48.86	0.25
7000	46.28	0.23
7200	43.46	0.22
7400	40.75	0.23
7600	38.87	0.25
7800	36.87	0.31
8000	33.64	0.29