

Typical Performance Data

FREQ.	Insertion Loss	Input Return Loss	Output Return Loss
(MHz)	(dB)	(dB)	(dB)
50.00	54.98	0.01	0.00
121.25	47.13	0.02	0.00
145.00	45.65	0.02	0.00
192.50	43.21	0.01	0.01
976.25	28.97	0.07	0.04
1000.00	28.76	0.06	0.05
1023.75	28.57	0.07	0.06
1047.50	28.37	0.08	0.07
1071.25	28.16	0.08	0.05
2021.25	22.80	0.23	0.20
2045.00	22.71	0.23	0.21
2068.75	22.61	0.23	0.21
2092.50	22.51	0.24	0.22
2116.25	22.42	0.25	0.21
3090.00	19.99	0.37	0.34
3113.75	19.97	0.37	0.34
3137.50	19.93	0.37	0.33
3161.25	19.89	0.37	0.34
3185.00	19.85	0.38	0.34
3968.75	19.18	0.39	0.37
3992.50	19.17	0.39	0.38
4016.25	19.17	0.39	0.38
4040.00	19.17	0.39	0.37
4063.75	19.18	0.39	0.37
7420.00	21.38	0.87	0.75
8000.00	4.42	6.30	6.27
8350.00	1.95	17.75	18.45
8400.00	1.91	16.51	17.11
8410.00	1.90	16.34	16.97
8410.63	1.90	16.34	16.95
8411.25	1.90	16.32	16.95
8411.88	1.90	16.32	16.94
8500.00	1.89	16.01	16.48
8550.00	1.89	16.85	17.29
8985.00	3.76	7.31	7.14
9782.50	19.39	1.13	0.92
9787.03	19.51	1.12	0.92
9791.56	19.64	1.12	0.91
9796.09	19.76	1.11	0.91
9800.63	19.89	1.10	0.90
10000.00	26.31	0.80	0.79
10946.88	23.82	0.43	0.72
10962.66	23.60	0.30	0.72
10978.44	23.45	0.20	0.72
10994.22	23.38	0.17	0.72
11010.00	23.35	0.19	0.72
11025.78	23.32	0.28	0.72
11041.56	23.25	0.43	0.73
12098.91	19.56	1.09	0.72
12114.69	19.56	1.15	0.71
12130.47	19.58	1.20	0.71
13535.00	20.97	0.61	0.61
13550.78	20.86	0.60	0.62
13566.56	20.80	0.65	0.62
13582.34	20.92	0.74	0.62
14040.00	22.91	1.02	0.58
14055.78	22.96	0.93	0.58
14071.56	23.03	0.82	0.58
15002.66	26.65	0.67	0.57
15050.00	28.33	1.04	0.59