

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
1000	57.13	2151.27	102.35
1100	53.26	510.31	95.79
1200	43.01	312.42	137.71
1210	42.38	292.63	134.70
1220	41.74	286.08	132.06
1230	41.15	274.53	131.32
1240	40.55	269.46	132.58
1250	40.02	261.73	135.69
1260	39.45	257.66	143.16
1270	38.91	249.99	147.83
1280	38.40	241.66	140.38
1290	37.91	234.02	127.78
1300	37.42	232.54	120.06
1400	33.20	188.77	154.95
1500	29.61	151.83	149.52
1600	26.34	120.64	168.41
1700	23.21	94.59	263.53
1800	20.05	69.37	562.59
2000	13.14	28.24	57.01
2200	4.95	5.40	5.97
2400	1.23	1.27	1.33
2404	1.24	1.29	1.35
2408	1.25	1.31	1.37
2412	1.25	1.33	1.39
2416	1.26	1.36	1.41
2420	1.27	1.38	1.43
2424	1.27	1.40	1.45
2428	1.28	1.42	1.46
2432	1.29	1.43	1.48
2436	1.29	1.45	1.49
2440	1.30	1.46	1.51
2444	1.30	1.48	1.52
2448	1.31	1.49	1.53
2452	1.32	1.50	1.54
2456	1.32	1.51	1.54
2460	1.33	1.52	1.55
2464	1.34	1.52	1.55
2468	1.34	1.52	1.55
2472	1.34	1.53	1.55
2476	1.35	1.53	1.55
2480	1.35	1.52	1.55
2484	1.36	1.52	1.54
2488	1.36	1.52	1.54
2492	1.37	1.51	1.53
2496	1.37	1.50	1.52
2500	1.37	1.49	1.51
2600	1.78	1.42	1.39
2800	9.27	11.64	14.09
3000	18.50	43.41	119.81
3200	26.35	81.54	1823.41
3400	34.03	121.49	183.80
3600	43.41	149.54	107.28
3650	46.26	153.22	102.28
3700	49.05	153.55	106.93
3750	50.56	158.11	96.65
3800	50.15	160.25	92.57
4000	44.80	166.76	85.19
4200	42.36	163.25	88.35
4400	41.33	146.42	100.77
4600	41.16	126.99	114.21
4800	41.42	113.00	110.49
4840	41.49	111.76	135.77
4880	41.57	110.03	116.11
4900	41.58	108.04	107.95
4920	41.67	108.40	106.77
4940	41.73	107.40	117.01
4960	41.81	107.35	132.79
4980	41.95	106.72	140.32
5000	41.99	105.25	130.75
5200	42.96	95.67	145.73
5400	44.29	86.60	146.26
5600	46.06	82.39	232.27
5800	48.64	83.85	180.64
6000	51.95	88.95	152.58