

## Typical Performance Data

FREQ.	INSERTION LOSS	INPUT RETURN LOSS (50Ω)	OUTPUT RETURN LOSS (75Ω)
(MHz)	(dB)	(dB)	(dB)
1.00	0.00	14.05	13.97
10.00	0.01	14.02	14.00
50.00	0.03	13.98	14.12
100.00	0.07	14.00	14.24
125.00	0.09	14.03	14.29
150.00	0.10	14.07	14.36
175.00	0.13	14.13	14.45
200.00	0.15	14.19	14.56
225.00	0.17	14.27	14.66
250.00	0.19	14.37	14.77
300.00	0.23	14.61	14.95
325.00	0.25	14.75	15.06
350.00	0.26	14.90	15.21
400.00	0.29	15.23	15.54
425.00	0.30	15.42	15.71
450.00	0.31	15.62	15.88
475.00	0.31	15.82	16.07
500.00	0.32	16.04	16.29
525.00	0.32	16.27	16.53
550.00	0.32	16.51	16.79
575.00	0.31	16.76	17.04
600.00	0.31	17.02	17.31
625.00	0.30	17.27	17.62
650.00	0.29	17.53	17.97
675.00	0.28	17.80	18.34
700.00	0.27	18.07	18.72
725.00	0.26	18.35	19.09
750.00	0.24	18.62	19.46
775.00	0.23	18.89	19.85
800.00	0.22	19.16	20.27
825.00	0.21	19.42	20.73
850.00	0.20	19.67	21.13
875.00	0.19	19.91	21.50
900.00	0.18	20.12	21.82
925.00	0.17	20.31	22.09
950.00	0.17	20.49	22.36
975.00	0.17	20.65	22.57
1000.00	0.17	20.77	22.65
1025.00	0.17	20.85	22.56
1050.00	0.17	20.88	22.37
1100.00	0.18	20.84	21.89
1150.00	0.19	20.69	21.17
1200.00	0.21	20.38	20.35
1250.00	0.23	19.96	19.67
1300.00	0.25	19.49	18.98
1350.00	0.26	18.96	18.36
1400.00	0.27	18.42	17.89
1450.00	0.27	17.88	17.43
1500.00	0.27	17.34	17.04
1600.00	0.26	16.41	16.49
1700.00	0.24	15.65	16.13
1800.00	0.24	15.13	15.93
1900.00	0.24	14.84	15.88
2000.00	0.27	14.84	15.93
2050.00	0.29	14.90	16.02
2100.00	0.31	15.02	16.16
2150.00	0.33	15.23	16.27
2200.00	0.35	15.51	16.45
2250.00	0.37	15.83	16.74
2300.00	0.38	16.23	17.01