

# RF Transformer

# TC1-1-43X+

## Typical Performance Data

FREQUENCY MHz	AVERAGE INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (deg.)
650.0	0.30	19.40	0.72	7.04
700.0	0.30	19.03	0.70	6.11
750.0	0.31	19.48	0.65	5.46
800.0	0.32	19.01	0.65	4.73
900.0	0.33	19.01	0.59	4.12
1000.0	0.35	18.85	0.50	3.45
1200.0	0.40	18.26	0.37	1.90
1400.0	0.42	17.29	0.27	1.06
1600.0	0.45	16.34	0.15	0.32
1800.0	0.48	15.68	0.04	0.37
2000.0	0.53	15.36	0.05	0.42
2200.0	0.58	15.34	0.18	0.52
2400.0	0.62	15.45	0.29	0.05
2600.0	0.62	16.20	0.40	0.66
2800.0	0.60	17.83	0.49	1.00
3000.0	0.57	20.76	0.56	1.07
3200.0	0.61	21.60	0.69	0.63
3400.0	0.75	16.64	0.74	1.98
3600.0	1.00	12.03	0.67	3.49
3800.0	1.34	9.18	0.41	4.79
3900.0	1.52	8.24	0.24	5.41
3950.0	1.61	7.64	0.20	5.57
4000.0	1.71	7.51	0.09	5.95



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

REV. X1  
TC1-1-43X+  
9/8/2011  
Page 1 of 1