

Typical Performance Data

FREQ.	INSERTION LOSS	INPUT RETURN LOSS (50Ω)	OUTPUT RETURN LOSS (75Ω)
(MHz)	(dB)	(dB)	(dB)
1.00	0.00	13.93	14.58
5.00	0.01	13.92	14.61
10.00	0.01	13.91	14.63
20.00	0.02	13.90	14.68
30.00	0.02	13.89	14.72
40.00	0.03	13.88	14.76
50.00	0.03	13.89	14.79
60.00	0.04	13.89	14.83
70.00	0.04	13.90	14.86
80.00	0.05	13.91	14.90
90.00	0.06	13.92	14.92
100.00	0.07	13.93	14.95
150.00	0.11	14.04	15.07
200.00	0.15	14.20	15.12
250.00	0.19	14.41	15.15
300.00	0.23	14.66	15.17
350.00	0.27	14.97	15.22
400.00	0.30	15.32	15.29
450.00	0.32	15.70	15.44
500.00	0.34	16.12	15.64
550.00	0.35	16.57	15.92
600.00	0.35	17.03	16.28
650.00	0.34	17.51	16.67
700.00	0.32	17.98	17.12
750.00	0.30	18.45	17.60
800.00	0.27	18.91	18.08
850.00	0.25	19.34	18.55
900.00	0.23	19.74	18.96
950.00	0.21	20.09	19.28
1000.00	0.21	20.41	19.52
1050.00	0.21	20.66	19.61
1100.00	0.22	20.85	19.52
1150.00	0.23	20.98	19.36
1200.00	0.25	21.04	19.12
1250.00	0.26	21.03	18.84
1300.00	0.27	20.97	18.62
1350.00	0.28	20.85	18.46
1400.00	0.29	20.66	18.35
1450.00	0.30	20.41	18.32
1500.00	0.30	20.10	18.38
1550.00	0.31	19.74	18.46
1600.00	0.32	19.35	18.54
1650.00	0.34	18.94	18.63
1700.00	0.36	18.52	18.65
1750.00	0.38	18.14	18.63
1800.00	0.40	17.79	18.58
1850.00	0.42	17.48	18.57
1900.00	0.44	17.24	18.57
1950.00	0.45	17.09	18.65
2000.00	0.45	17.02	18.88
2050.00	0.45	17.04	19.26
2100.00	0.44	17.18	19.78
2150.00	0.43	17.41	20.61
2200.00	0.42	17.74	21.66
2250.00	0.41	18.13	23.02
2300.00	0.41	18.51	24.68
2350.00	0.41	18.82	26.54
2400.00	0.42	18.93	28.45
2450.00	0.43	18.78	29.59
2500.00	0.44	18.36	29.25