

Surface Mount Bandpass Filter

SXBP-615+

50Ω 565 to 670 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W Max.

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

INPUT	1
OUTPUT	8
GROUND	2, 3, 4, 5, 6, 7

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F		
.44	.74	.27	.200	.07	.060		
11.18	18.80	6.86	5.08	1.78	1.52		
G	H	J	K	L	M	wt.	
.040	.660	.200	.470	.055	.060	grams	
1.02	16.76	5.08	11.94	1.40	1.52		3.0

Note: Please refer to case style drawing for details

Demo Board MCL P/N: TB-368 Suggested PCB Layout (PL-230)




- NOTE:
- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS: .025±.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- high rejection
- flat group delay @ passband
- good VSWR, 1.3:1 typ @ passband
- shielded case
- aqueous washable

Applications

- mobile TV
- receivers / transmitters
- harmonic rejection



Generic photo used for illustration purposes only

CASE STYLE: HF1139


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Bandpass Filter Electrical Specifications (T_{AMB} = 25°C)

CENTER FREQ. (MHz)	PASSBAND (MHz) (Loss < 4dB)	STOPBANDS (MHz)				VSWR (:1)		
		Loss > 20dB	Loss > 40dB			Passband	Stopband	
F _c	F ₁ - F ₂	F ₃	F ₄	F ₅	F ₆	Typ.	Max.	Typ.
615	565 - 670	380	720	250	740 - 2300	1.3	1.9	20

Typical Frequency Response






Functional Schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nSec)
	\bar{x}	σ			
0.5	93.98	3.00	0.01	555.0	5.20
250.0	52.72	0.29	0.05	560.0	5.27
380.0	29.65	0.41	0.25	565.0	5.30
430.0	17.34	0.64	0.80	570.0	5.32
450.0	11.22	0.78	1.85	580.0	5.33
470.0	5.30	0.60	6.58	590.0	5.36
565.0	1.43	0.04	12.98	600.0	5.45
580.0	1.30	0.02	17.97	610.0	5.68
615.0	1.42	0.05	22.32	615.0	5.84
640.0	1.74	0.08	18.33	620.0	5.99
670.0	2.58	0.08	12.75	630.0	6.21
690.0	6.56	1.62	7.05	640.0	6.63
700.0	13.84	2.34	3.07	650.0	7.32
710.0	22.42	2.46	1.95	660.0	8.19
720.0	31.31	2.80	1.46	670.0	9.71
740.0	53.80	3.72	1.01	673.0	10.51
1000.0	55.59	0.27	0.23	676.0	11.48
2300.0	56.85	0.49	0.34	680.0	13.06



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. C
ECO-005139
EDR-9159AUF1
SXBP-615+
URJ/RAV
201202
Page 1 of 1