

# Coaxial Band Pass Filter

# ZFBP13-75+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.3	97.25	0.01
1	102.14	0.01
5	87.34	0.05
7	76.63	0.09
8	72.29	0.13
9	67.70	0.21
10	57.83	0.38
11	39.87	0.67
12	3.11	17.86
13	2.76	17.71
14	2.97	19.18
15	16.86	2.53
16	36.14	0.83
17	49.40	0.44
18	54.55	0.36
20	72.27	0.16
25	82.32	0.08
35	91.36	0.07
50	87.48	0.07
100	81.25	0.09
120	77.26	0.09
140	75.14	0.09
160	74.81	0.10
180	72.29	0.10
200	71.14	0.11
220	70.64	0.11
240	68.73	0.12
260	67.21	0.13
280	63.25	0.15
300	65.31	0.19
320	64.84	0.30
330	62.90	0.44
340	60.22	0.72
350	50.93	1.03
360	44.71	0.84
380	38.23	0.40
390	33.89	0.35
400	29.40	0.37
420	29.08	0.33
440	27.87	0.55
450	25.71	1.03
460	24.80	1.54
470	27.55	0.97
480	31.05	0.55
500	36.09	0.29
550	42.16	0.20
600	44.71	0.18
650	45.87	0.18
700	46.37	0.19
750	46.61	0.20
800	46.45	0.21
850	46.40	0.22
900	45.99	0.24
950	45.68	0.26
1000	45.23	0.31

REV. X1  
ZFBP13-75+  
061119  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

