




### THE BIG DEAL

- Wideband, 2 to 18 GHz
- Flat Gain 16.6±0.7 dB from 2 to 18 GHz
- P1dB, +19.6 dBm Typ. at 10 GHz.
- OIP3, +27.4 dBm Typ. at 10 GHz.

### APPLICATIONS

- 5G MIMO and Back Haul Radio Systems
- Satellite Communications
- Test and Measurement Equipment
- Radar, EW, and ECM Defense Systems



**+RoHS Compliant**  
 The +Suffix identifies RoHS Compliance.  
 See our website for methodologies and qualifications

SEE ORDERING INFORMATION ON THE LAST PAGE

### PRODUCT OVERVIEW

The AVA-2183-D+ is an amplifier die that operates from 2 to 18 GHz that is fabricated on a GaAs PHEMT MMIC process. The Amplifier provides 16.6 dB of Gain, +27.6 dBm OIP3 and +19.7 dBm Output Power at 1 dB Compression point with 16 dB typical Return Loss while requiring +4V and 210 mA DC power. Gain flatness is +/- 0.7 dB across the operating bandwidth. The Amplifier is ideal for use in very wideband ECM, Test & Measurement and Microwave communications systems.

### KEY FEATURES

Feature	Advantages
Wideband: 2 to 18 GHz <ul style="list-style-type: none"> <li>• 16 dB Gain Typ. at 2 GHz</li> <li>• 17 dB Gain Typ. at 18 GHz</li> </ul>	Suitable for wide bandwidth defense and test and measurement application as well as narrow band performance driven applications.
Good P1dB & OIP3 <ul style="list-style-type: none"> <li>• +19.6 dBm P1dB Typ. at 10 GHz</li> <li>• +27.4 dBm OIP3 Typ. at 10 GHz</li> </ul>	Suitable as a driver amplifier in receiver/transmitter chains.
High Reverse Isolation	Isolates adjacent circuitry without need for an external expensive isolator.
Input and Output Return Loss	Eliminates need for external matching circuit providing published Return Loss.
Unpackaged Die	Suitable for chip and wire hybrid assemblies.

**ELECTRICAL SPECIFICATIONS<sup>1</sup> AT 25°C, VDD=+4V, IDD=210mA & Zo=50Ω UNLESS NOTED OTHERWISE**

Parameter	Condition (GHz)	VDD=+4V			Units
		Min.	Typ.	Max.	
Frequency Range		2		18	GHz
Gain	2		15.9		dB
	5		16.1		
	10		17.2		
	15		16.7		
	18		16.9		
Input Return Loss	2		12		dB
	5		16		
	10		14		
	15		11		
	18		14		
Output Return Loss	2		18		dB
	5		20		
	10		19		
	15		16		
	18		15		
Reverse Isolation	2 - 18		47.4		dB
Output Power at 1dB Compression	2		18.9		dBm
	5		19.3		
	10		19.6		
	15		18.2		
	18		17.6		
Output Third-Order Intercept (Pout = 0 dBm/Tone)	2		31.2		dBm
	5		29.1		
	10		27.4		
	15		25.2		
	18		23.7		
Noise Figure	2		6.8		dB
	5		6.4		
	10		5.5		
	15		4.7		
	18		5.1		
Device Operating Voltage (VDD)			+4		V
Device Operating Current (IDD)			210		mA
Device Gate Voltage (VGG)			-0.46		V
Device Gate Current (IGG)			-0.2		μA
Thermal Resistance, Junction-to-Ground Lead (ΘJC)			38.8		°C/W

1. Die is soldered and measured on Mini-Circuits die characterization board. See characterization circuit (Fig. 1).



MMIC DIE

# Wideband Amplifier

## AVA-2183-D+

Mini-Circuits

50Ω 2 to 18 GHz


### MAXIMUM RATINGS<sup>2</sup>

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to +85°C
Junction Temperature	+150°C <sup>3</sup>
Power Dissipation	1.7W
Input Power (CW)	+23 dBm (5 minute max) +14 dBm (continuous)
DC voltage on RF-OUT	+7V
Current I <sub>GG</sub>	-5mA to 0mA
Current I <sub>DD</sub>	320mA
DC Voltage on V <sub>DD</sub> (V <sub>DD1</sub> & V <sub>DD2</sub> )	+7V
DC Voltage on V <sub>GG</sub> (V <sub>GG1</sub> & V <sub>GG2</sub> )	-1.5 V to -0.2 V

2. Permanent damage may occur in any of these limits are exceeded. Electrical maximum ratings are not intended for continuous normal operation.


3. T<sub>j</sub> = +85°C + (V<sub>DD</sub>)\*(I<sub>DD</sub>)\*(θ<sub>JC</sub>) = +117°C. Keeping T<sub>j</sub> below +117°C will ensure MTTF > 100 Years.

### SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Pad Number	Description
RF-IN	1	RF Input Pad
GROUND	2, 5, 7, 10, & Bottom of die	The bond pads are connected to backside through vias and do not require wire-bond connections to ground.
VGG1	3	Gate Bias Pad #1
VGG2	4	Gate Bias Pad #2
RF-OUT	6	RF Output Pad
VDD2	8	Drain Bias Pad #2
VDD1	9	Drain Bias Pad #1

### BONDING PAD POSITION




### DIMENSION IN μM, TYP.

L1	L2	L3	L4	L5	L6	L7
95	211	422	1328	1767	2519	2614
H1	H2	H3	H4	H5	H6	
98	312	462	612	1343	1438	
Thickness	Die size	Pad size 1 & 6	Pad size 2,3,5,7,8,9 & 10	Pad size 4		
100	2614 x 1438	93 x 113	93 x 93	96 x 96		





## CHARACTERIZATION &amp; APPLICATION CIRCUIT



Component	Size	Value	Part Number	Manufacturer
C2, C3, C5 & C6	100pF	22x22mil	MA4M3100	MACOM
C1 & C4	0.1uF	0402	GRM155R71A474KE01D	Murata
C7 & C8	10uF	1206	CL31B106KBHNNNE	Samsung

Fig.1: Characterization &amp; Application Circuit

Note: This block diagram is used for characterization (Die is attached and wire-bonded on a die characterization test board). Gain, Return Loss, Output Power at 1dB Compression (P1dB), Output IP3 (OIP3) and Noise Figure are measured using Agilent's N5242A PNA-X Microwave Network Analyzer.

## Conditions:

1. VDD = +4V
2. VG is set to obtain desired IDD as shown in specification table.
3. Gain and Return Loss: Pin = -25 dBm
4. Output IP3 (OIP3): Two Tones, spaced 1 MHz apart, 0 dBm/Tone at Output.

## Power ON Sequence:


- 1) Set VGG = -1.3V. Apply VGG.
- 2) Set VDD = +4V. Apply VDD.
- 3) Increase VGG to obtain desired IDD as shown in specification table.
- 4) Apply RF Signal

## Power OFF Sequence:

- 1) Turn off RF Signal.
- 2) Adjust VGG down to -1.3V.
- 3) Turn off VDD.
- 4) Turn off VGG.




## ASSEMBLY DIAGRAM



Note: Tested on die characterization board with following bond lengths:

1. Typical bond length for RF-IN: 280μm (11mils)
2. Typical bond length for RF-OUT: 280μm (11mils)
3. Typical bond lengths from die, capacitor, VDD1, VDD2, VGG1, and VGG2 were kept as short as possible
4. Component list given in Figure 1.

## ASSEMBLY AND HANDLING PROCEDURE

1. **Storage**  
Die should be stored in a dry nitrogen purged desiccators or equivalent.
2.  **ESD**  
MMIC PHEMT amplifier die are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be open in clean room conditions at an appropriately grounded anti-static workstation.
3. **Die Handling and Attachment**  
Devices need careful handling using correctly designed collets, it is recommended to handle the chip along the edges with a custom design collet. The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are Ablestik 84-1 LMISR4 or equivalents. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. The surface of the chip has exposed air bridges and should not be touched with vacuum collet, tweezers or fingers.
4. **Wire Bonding**  
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the Die gold bond pads. Thermo-sonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1mil diameter. Bonds must be made from the bond pads on the die to the packaged or substrate. All bond wire length and bond wire height should be kept as short as possible unless specified by the Assembly Drawing to minimize performance degradation due to undesirable series inductance.



**MMIC DIE**

# Wideband Amplifier

**AVA-2183-D+**

Mini-Circuits®

50Ω 2 to 18 GHz

**ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD.**

<b>Performance Data</b>	Data Table
	Swept Graphs
	S-Parameter (S2P Files) Data Set with and without port extension(.zip file)
<b>Case Style</b>	Die
<b>Die Ordering and packaging information</b>	Quantity, Package                                  Model No.
	Gel - Pak: 5,10,50,100 KGD*                      AVA-2183-DG+ Medium†, Partial wafer: KGD*<570      AVA-2183-DP+ Full wafer    AVA-2183-DF+
	†Available upon request contact sales representative Refer to AN-60-067
<b>Die Marking</b>	EL-AMP-11-2
<b>Environmental Ratings</b>	ENV80

\*Known Good Die ("KGD") means that the die in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such die fall within a predefined range. While DC testing is not definitive, it does provide a higher degree of confidence that die are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

**NOTES**

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained there in. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)
- D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an As is basis, with all faults.
- E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Die (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Die.
- F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.

