



Outline Dimensions



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK



CASE #	A	B	C	D	E	F	G	H	J	K	L
AW1564	3.00 (76.20)	2.06 (52.32)	2.03 (51.56)	.10 (2.54)	2.500 (63.50)	1.525 (38.74)	.125 (3.18)	.50 (12.70)	.50 (12.70)	.50 (12.70)	2.00 (50.80)

CASE #	M	N	WT, GRAMS	WT WITHOUT HEATSINK, GRAMS
AW1564	1.00 (25.40)	2.00 (50.80)	230	165

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heat sink finish: Black anodize.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS