

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMP-FEMALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMP-FEMALE 2 RETURN LOSS (dB)
10	0.01	49.79	51.47
100	0.06	41.73	42.26
200	0.09	42.34	43.69
300	0.11	47.74	48.32
400	0.13	51.41	46.70
500	0.15	53.70	48.13
600	0.16	59.99	55.18
700	0.18	44.44	43.26
800	0.19	40.54	39.91
900	0.20	40.95	41.43
1000	0.21	43.44	46.39
1100	0.23	39.55	40.40
1200	0.24	36.26	36.61
1300	0.25	35.94	36.32
1400	0.26	37.48	38.48
1500	0.26	36.43	38.21
1600	0.27	33.82	35.06
1800	0.29	35.14	34.48
2000	0.31	31.95	32.70
2500	0.35	30.12	30.59
3000	0.39	28.97	29.35
3500	0.41	29.78	29.18
4000	0.43	28.74	29.98
4500	0.47	26.97	28.73
5000	0.52	25.99	26.73
5500	0.54	26.43	26.17
6000	0.55	28.51	27.58
6500	0.56	28.17	31.14
7000	0.60	24.21	26.49
7500	0.64	21.91	22.48
8000	0.66	22.85	22.77
8500	0.65	29.29	29.20
9000	0.66	33.46	35.60
9500	0.69	23.48	23.24
10000	0.74	19.96	19.80
10500	0.74	20.80	20.44
11000	0.73	28.19	26.09
11500	0.75	31.00	24.91
12000	0.78	21.69	20.22
12500	0.79	19.44	19.11
13000	0.80	20.60	20.48
13500	0.81	26.80	20.76
14000	0.82	30.73	21.75
14500	0.85	21.22	19.79
15000	0.86	20.08	19.74
15500	0.86	21.07	21.37
16000	0.88	25.38	22.56
16500	0.89	40.50	24.69
17000	0.91	27.73	25.99
17500	0.92	25.41	25.80
18000	0.94	25.30	26.16